

SAMZO | REAC/ROHS

REV	ECN NO	DESRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	Replace frame			2018.06.12



Technical Requirements

1. Frequency: 0~6GHz
2. Impedance: 50Ω
3. VSWR (Voltage Standing Wave Ratio): ≤1.35
4. Operating Voltage: 335V
5. Withstand Voltage: 1000V
6. Insulation Resistance: ≥5000MΩ
7. Contact Resistance: Inner conductor ≤3mΩ; Outer conductor ≤2mΩ
8. Insertion Loss: ≤0.5dB
9. Unspecified tolerances: ±0.2



SMA-KFD3-125-L0-0

- Surface treatment镀层:镀金
- Direction方向:方形 垂直
- Length体长:12.5mm
- Product number编号:KFD3
- Product series系列:SMA同轴射频天线座

ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR					
C	插孔	HPB59-1	1	------				GENERAL TOLERANCE	
B	绝缘体	聚四氟乙烯	1	------				≥0~2<	±0.15
A	主体	黄铜	1	镀金	DESIGN	WANGGUIFA	2018.06.12	≥2~5<	±0.25
					CHECKED	ZHENGUILAN	2018.06.12	≥0~2<	±0.15
					APPROVED	LILIANJIANG	2018.06.14	≥5	±0.35

FIRST VIEW

SCALE 1:1 UNIT mm

The copyright belongs to samzo parts [China] Co., Ltd. please use the material after samzo parts agree to authorize. The final right of interpretation belongs to samzo parts.
WWW.KKK-JP.COM

SAMZO COMPONENTS
Electronic switch and connector manufacturer

TITLE:: SMA-KFD3-方型 垂直
DWG NO: SMAKFD3-P050
PART NO: SMAKFD3-180671
MODEL NO: SMA-KFD3-125-L0-0
NAME: SMA COAXIAL RF CONNECTOR