

General Characteristics




V_R	I_F	$V_{F(type)}$	I_{FSM}	T_{jmax}
75V	150mA	0.98V	2A	150°C

Features

- SOT23 Package
- Epoxy meets UL-94 V-0 flammability rating and halogen free
- Moisture Sensitivity Level 1
- High temperature soldering guaranteed 260°C/10seconds
at terminals

Application

- Extreme fast switches
- Automotive



Package Marking and Ordering Information

Product ID	Package	Marking	Qty(PCS)
MMBD4148	SOT23	KA2	3000





Absolute Maximum Ratings (Ta=25°C unless otherwise noted)

Parameter	Symbols	MMBD4148	Units
Repetitive peak reverse voltage	VRRM	100	V
DC Blocking Voltage	VR	75	V
Average forward current	IFAV	150	mA
Peak forward surge current(tp=1us)	IFSM	2	A
Power dissipation	PD	350	mW
Thermal Resistance Junction to Ambient Air	R θ JA	357	°C/W
Junction temperature	Tj	-55~150	°C
Storage temperature range	Tstg	-55~150	°C

Note: 1. Device mounted on an FR4 Printed-Circuit Board (PCB), single-side copper, tin-plated and standard footprint.


Electrical Characteristics (T_J=25°C , unless otherwise noted)

Parameter	Symbols	Test Conditions	Min	Type	Max	Units
Forward Voltage	V _{F1}	I _F =1mA		0.59	0.715	V
	V _{F2}	I _F =10mA		0.71	0.855	
	V _{F3}	I _F =50mA		0.83	1.0	
	V _{F4}	I _F =150mA		0.98	1.25	
Reverse Current	I _{R1}	V _R =20V			0.025	μA
	I _{R2}	V _R =75V			2.5	
Breakdown Voltage	V _R	I _R =100 μA	75			V
Diode Capacitance	C _j	V _R =V _F =0V, f =1MHZ			2	pF
Reverse Recovery Time	t _{rr}	I _F =I _{rr} =10mA, I _{rr} =0.1I _R , R _L =100 Ω			4	ns


Ratings And Characteristic Curves


Package Information


Carrier Dimension(mm)



Dimensions are in millimeter															
Pkg Type	A0	A1	B0	B1	K0	D0	D1	E	F	P0	P1	P2	10*P0	W	T
SOT-23	3.15	1.09	2.77	2.15	1.22	1.55	1.00	1.75	3.50	4.00	4.00	2.00	40.00	8.00	0.20
Tolerance	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.1	±0.2	±0.1	±0.03



Reel Dimension(mm)




Reel Option	D	D1	D2	G	H	I	W1	W2
7"Dia	Φ178.00	54.40	13.00	R78.00	R25.60	R6.50	9.50	12.30
Tolerance	±2	±1	±1	±1	±1	±1	±1	±1

Package Specifications


Package	Reel Size	Reel DIA. (mm)	Q'TY/Reel (Kpcs)	Box Size (mm)	QTY/Box (Kpcs)	Carton Size (mm)	Q'TY/Carton (Kpcs)
SOT23	7'	178	3	210*208*203	45	440*400*230	180

Recommended Soldering Profile for Rectifier Diodes (Pb Free)

a) Wave Soldering Profile





b) Reflow Soldering Profile (Pb Free Application), refer to IPC/JEDEC J-STD-020



Preheat/Soak Temperature Min (T _{min}) Temperature Max (T _{max}) Time (ts) from (T _{min} to T _{max})	50 °C 200 °C 60-120 seconds
Melting Point of Solder (Sn Ag Cu)	217°C
Ramp-up Rate to 217°C(Melting Point of Solder)	3°C/sec
Time at Temp.>217°C (Melting Point of Solder)	60~150 Sec
Peak Temperature	255±5°C
Time within 5°Cbelow Peak Temp.	20~40 Sec
Cooling Rate	6°C/sec (max)
Time from 25°C to Peak Temp.	8min (max)

c) Manual Soldering

When using an electric soldering iron for manual soldering, it is recommended that the temperature does not exceed 300 °C and the soldering time is less than 10 seconds.

Package Mechanical Data

Suggested Pad Layout

Note:

1. Controlling dimension: in millimeters.
2. General tolerance: $\pm 0.05\text{mm}$.
3. The pad layout is for reference purposes only.

Disclaimer

The information presented in this document is for reference only. Yancheng **Xirun Semiconductor Co., Ltd** reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise.

The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), **Xirun Semiconductor** or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale.

This publication supersedes & replaces all information previously supplied. For additional information, please visit our website <http://www.x-semi.cn>, or consult your nearest **Xirun Semiconductor's** sales office for further assistance.