








PCB 参考安装方式

NOTES:

备注

- 1.Brass or purple copper,tin-plating
黄铜, 镀锡
- 2.Wire screw hole M5(M3,M4)
压线螺孔M5(M3,M4)可定制
- 3.Current Rating: 60A
额定电流:60A
- 4.There shall be no defects such as
pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差
- 6.扭矩: 2.03 Nm

Ordering Information

HC - * ** * - **** - D *** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series	Dip	Product No.	Material
Full Teeth (插牙)	0.8mm	M5 (螺牙)	0.8mm	0808x8mm	SMT	默认	Copper
Partial Teeth (半插牙)	1.0mm	M5 (螺牙)	1.0mm	1010x10mm	HT	产品序号	紫铜
Partial Teeth (半插牙)	1.2mm	M5 (螺牙)	1.2mm	1212x12mm	HT	产品序号	紫铜
Partial Teeth (半插牙)	1.5mm	M5 (螺牙)	1.5mm	1515x15mm	HT	产品序号	紫铜
Partial Teeth (半插牙)	2.0mm	M5 (螺牙)	2.0mm	2020x20mm	HT	产品序号	紫铜
Partial Teeth (半插牙)	2.5mm	M5 (螺牙)	2.5mm	2525x25mm	HT	产品序号	紫铜
Partial Teeth (半插牙)	3.0mm	M5 (螺牙)	3.0mm	3030x30mm	HT	产品序号	紫铜
Partial Teeth (半插牙)	3.2mm	M5 (螺牙)	3.2mm	3232x32mm	HT	产品序号	紫铜



GENERAL TOLERANCE			制图	07	深圳市华灿天禄电子有限公司			
DIM TOL			审核		ShenzhenhuacantianluELECTRONICS CO.,LTD			
5 or more ±0.35			批准		产品名称	PCB 焊接端子 厚度1.0 插板 铜垫片	版本	A
2~5 ±0.25			比例		TITLE	M5 4焊脚 10x8.6x19mm	REV.	
0~2 ±0.15			SCALE		产品料号	HC-RG1054-1008-D339-07	单位	mm
Angle ±3.0°			投影		PART NO.		页次	1/1
序号	变更内容	日期	材料		MATERIAL		SHEET	
No.	MODIFY CONTENT	MODIFY DATE						