







NOTES:
备注

1. Brass or purple copper, tin-plating
   黄铜，镀锡
2. Wire screw hole M4(M3, M5)
   压线螺孔M4(M3, M5)可定制
3. Current Rating: 70A
   额定电流:70A
4. There shall be no defects such as pin deformation and burrs.
   不得有脚变形，毛刺等缺陷
5. Unmarked dimensions refer to tolerances
   未标注的尺寸参考公差
6. 扭矩：1.47Nm

Ordering Information

HC - * ** * * - **** - * *** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series		Product No.	Material
1=Full Teeth (满牙) 2=Insert Nut (带螺母) 3=Insert Gasket (带垫片)	10=1.0mm 12=1.2mm 15=1.5mm 20=2.0mm 25=2.5mm 30=3.0mm 40=4.0mm 50=5.0mm 60=6.0mm 80=8.0mm 10=1.2mm	M3=M3 (螺牙) M4=M4 (螺牙) M5=M5 (螺牙)	2=2个 3=3个 4=4个 5=5个 6=6个 8=8个	0808=8x8mm 1820=18x20mm	1=HP 2=HH 3=Tag Hip	产品序号	默认=Copper (黄铜) HC=Red Copper (紫铜)



序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE
1	初版发行	

GENERL TOLERANCE	
DIM	TOL
5 or more	±0.35
2~5	±0.25
0~2	±0.15
Angle	±3.0°

制 图 DRAWING	07	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD	
审 核 CHECK			
批 准 APPROVAL		产品名称 TITLE	PCB 焊接端子 厚度1.5 平贴片 抽牙 M4 18x8.5x3mm
比 例 SCALE		产品料号 PART NO.	HC-M1540-1808-S736-07
投 影 Projection		材 料 MATERIAL	

版 本 REV.	A
单 位 UNITS	mm
页 次 SHEET	1/1