









REV.	ECN NO OR DESCRIPTION	REVISED	DATE



- NOTES—
- 1.Electrical:
Contact resistance:50m ohms max.
Dielectric withstanding voltage:500V RMS.
Insulation resistance:1000M ohms min.
 - 2.Mechanical:
MATE AND UNMATE FORCE:
MATE FORCE:4.5kg MAX
UNMATE FORCE:0.5kg MIN
Durability:1500cycles MIN.
 - 3.Environment:
Operating Temperature:−25°to+85°.
 - 4.FINISH:
TERMINAL: GOLD Plated Over NICKEL
Contact area,TIN ON
SOLDER TAIL AREA& TIN
Plated ALL Over NICKEL.
Shell: SPCC WITH NICKEL&GOLD Plated.
 - 5.COLOR:
HOUSING:BLACK.



Pin No.	NAME
1	DAT2
2	CD/DAT3
3	CMD
4	VDD
5	CLK
6	VSS
7	DAT0
8	DAT1

序号	DIM A	料号
1	2.55H	TF-028-H255
2	2.65H	TF-028-H265
3	2.85H	TF-028-H285
4	3.00H	TF-028-H300
5	3.35H	TF-028-H335
6	3.75H	TF-028-H375
7	5.20H	TF-028-H520

UNLESS OTHERWISE SPECIFIED TOLERANCES				东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD				
DECIMALS:		ANGLES:		TITLE 短型 TF CARD 无侦测 H=2.65-5.2H				
X	±0.45	X	±2°	DWN	xiong	PART NO. TF-028-HXXX		
X.X	±0.35	X.X	±1°	CHKD	lee	SCALE:1:1	UNIT: mm	
X.XX	±0.25			APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4
CUSTOMER COPY								