




NOTES:

备注

- 1.Brass or purple copper,matte tin-plating
黄铜或紫铜，镀雾锡
- 2.Wire screw hole M4
压线螺孔M4
- 3.Current Rating: 60A
额定电流:60A
- 4.Screw Hole Standard Torque: 13 lbf.in $\approx$ 1.47 N/m
螺孔标准扭矩: 13 lbf.in $\approx$ 1.47 N/m
- 5.Operating Temperature: -40℃~+125℃
工作温度:-40℃~+125℃
- 6.Has passed the 72 hour salt spray test
已通过72小时盐雾测试
- 7.There shall be no defects such as
pin deformation and burrs.
不得有脚变形，毛刺等缺陷
- 8.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差

Ordering Information

HC	-	*	**	*	*	-	****	-	D	***	*	-	07
Type	Wet-11 Teeth	Thickness	Screw Thread	Welding Feet	Series	D-BIP	Product No.	Material					
	(抽牙)	08-0.8mm	3-M3 (螺牙)	(焊脚)	0808-8x8mm	S-MT	产品序号	默认-Copper					
	BN-Rivet Nut	10-1.0mm	4-M4 (螺牙)		1620-16x20mm	FD-Flag		(黄铜)					
	(铆螺母)	12-1.2mm	6-M6 (螺牙)			Dip		BC-Red Copper					
	RG-Rivet Gasket	15-1.5mm						(紫铜)					
	(铆垫片)	20-2.0mm											
		25-2.5mm											
		30-3.0mm											
		32-3.2mm											

PCB 参考安装方式



			GENERAL TOLERANCE	制 图	07	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审 核					
			5 or more $\pm$ 0.35	批 准		产品名称	PCB 焊接端子 厚度1.2 插板 抽牙	版 本	A
			2~5 $\pm$ 0.25	APPROVAL		TITLE	M4 4焊脚 9.1x9.1x10.5mm	REV.	
			0~2 $\pm$ 0.15	比 例		产品料号	HC-M1244-0909-D529-07	单 位	mm
			Angle $\pm$ 3.0°	SCALE		PART NO.		UNITS	
序号	变更内容	日期	投影	投 影		材 料		页 次	1/1
No.	MODIFY CONTENT	MODIFY DATE	Projection			MATERIAL		SHEET	