



NOTES:

备注

- 1.Brass or purple copper,tin-plating
黄铜，镀锡
- 2.Wire screw hole M5 (M3,M4)
压线螺孔M5 (M3,M4) 可定制
- 3.Current Rating: 70A
额定电流:70A
- 4.There shall be no defects such as
pin deformation and burrs.
不得有脚变形，毛刺等缺陷
- 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差
- 6.扭矩: 2.03 Nm

Ordering Information

HC	-	*	**	*	*	-	****	-	D	****	*	-	07
Type		Thickness		Screw		Welding		Series		[D=]P	Product No.		Material
(Type)		(mm)		Thread		Feet		(mm)		S=MT	产品序号		默认Copper
(Type)		(mm)		(mm)		(mm)		1620mm		P=Tag			PCB铜
(Type)		(mm)		(mm)		(mm)				Tag			(紫铜)
(Type)		(mm)		(mm)		(mm)				Tag			(紫铜)

工程专用章

		GENERAL TOLERANCE	制 图	07	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD		
		DIM TOL	审 核				
		5 or more ±0.35	批 准		产品名称	PCB 焊接端子 厚度1.2 插板 抽牙	版 本
		2~5 ±0.25	APPROVAL		TITLE	M5 4焊脚 9.1x9.1x10.5mm	REV.
		0~2 ±0.15	比 例		产品料号	HC-M1254-0909-D538-07	单 位
		Angle ±3.0°	SCALE		PART NO.		UNIT
			投 影		MATERIAL		页 次
			Projection				SHEET