



NOTES:

备注

- 1.Brass or purple copper,tin-plating
黄铜, 镀锡
- 2.Wire screw hole M3(M4,M5)
压线螺孔M3(M4,M5)可定制
- 3.Current Rating: 60A
额定电流:60A
- 4.There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差
- 6.扭矩: 0.79 Nm

Ordering Information

HC - * ** * - **** - D *** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series	D=0.1P	Product No.	Material
Full Teeth (插牙)	0.8mm	M3 (螺牙)	0.8mm	0808x8mm	S=0.1P	产品序号	默认=Copper
Partial Nut (螺螺母)	1.2mm	M4 (螺牙)	2mm	1620x16x20mm	H=0.1P		(黄铜)
Partial Gasket (螺垫片)	1.5mm	M5 (螺牙)	4mm				Red Copper
	2.0mm	M6 (螺牙)	6mm				(紫铜)
	2.5mm		8mm				
	3.0mm						
	3.2mm						

GENERAL TOLERANCE			制图	07	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			审核					
5 or more			批准		产品名称	PCB 焊接端子 厚度1.0 插板 铜垫片	版本	A
2~5			比例		TITLE	M3 4焊脚 9x6.5x17.5mm	REV.	
0~2			SCALE		产品料号	HC-RG1034-0906-D335-07	单位	mm
Angle			投影		PART NO.		页次	1/1
序号	变更内容	日期	材料		MATERIAL		SHEET	
No.	MODIFY CONTENT	MODIFY DATE						