




NOTES:

备注

- 1.Brass or purple copper,tin-plating
黄铜或紫铜, 镀锡
- 2.Wire screw hole M5 (M4, M6)
压线螺孔M5 (M4, M6) 可定制
- 3.Current Rating: 80A
额定电流:80A
- 4.There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差
6. 扭矩: 2.03Nm

Ordering Information

HC - * ** * - **** - * ** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series	Welding Feet	Product No.	Material
Pin (插针)	0.5~1.0mm	M3 (螺牙)	1620~1620mm	0.5~1.0mm	1620~1620mm	1620~1620mm	0.5~1.0mm
Pin Nut (螺母)	1.0~1.5mm	M3 (螺牙)	1620~1620mm	0.5~1.0mm	1620~1620mm	1620~1620mm	0.5~1.0mm
Pin Gasket (垫片)	1.0~1.5mm	M3 (螺牙)	1620~1620mm	0.5~1.0mm	1620~1620mm	1620~1620mm	0.5~1.0mm



GENERAL TOLERANCE			制图	07	深圳市华灿天禄电子有限公司		
DIM TOL			审核		ShenzhenhuacantianluELECTRONICS CO.,LTD		
5 or more			批准		产品名称	PCB 焊接端子 厚度1.2 插板 抽牙	版本
2~5			比例		TITLE	M5 4焊脚 11.1x9.1x12.5mm	REV.
0~2			SCALE		产品料号	HC-M1254-1109-D543-07	UNIT
Angle			投影		PART NO.		mm
序号	变更内容	日期	材料		MATERIAL		页次
No.	MODIFY CONTENT	MODIFY DATE	Projection				SHEET