





NOTES:
1. MATERIAL:
HOUSING:LCP 30% G/F UL94V-0
COLOR:BLACK
CONTACT:BRASS T=0.25mm
2. FINISH:
CONTACT:GOLD FLASH PLATING ON CONTACT AREA
100u"MIN. TIN PLATING ON SOLDERTAILS
50u"MIN. NICKEL UNDERPLATING OVER ALL
BOARD LOCK:100u"MIN. TIN PLATING ON SOLDERTAILS
50u"MIN. NICKEL UNDERPLATING OVEER ALL
3. ELECTRICAL:
CURRENT RATING:1.5 AMPERE PER CONTACT
CONTACT RESISTANCE:30 mΩ MAX
INSULATION RESISTANCE:1000 MΩ MIN
DIELECTRIC WITH STANDING VOLTAGE:500 VDC
OPERATING TEMPERATURE: -40° C ~ +85° C

环保要求		产品必须符合ROHS要求			
3	Peg	Brass C2680		Tin/Ni Plated	
2	Terminal	Brass C2680		Gold/Tin Plated	
1	Housing	High Temp	Black	UL 94V-0	
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK	
GENERAL TOLERANCES UNLESS SPECIFIED		 HMTCONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
.X±0.30	.X°±3°	PART NO. HMT-SATA15G-S01	TITLE: SATA 15P公座90度 DIP型带鱼叉针长2.30mm		
.XX±0.20	.XX°±2°				
.XXX±0.05	.XXX°±0.5°				
MANUFACTURE DWG		DESIGN: James	CUSTOMER	SIZE	UNITS
		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
				N:A	1/1