





SPECIFICATION:
1. MATERIAL:
HOUSING: LCP UL 94V-0
COLOR:BLACK
CONTACT: PHOSPHOR BRONZE C5191R-H, T=0.25mm
PEG: BRASS C2680R-H, T=0.30mm
2. FINISH:
CONTACT:1u"/3u"/5u"/15u" GOLD PLATING ON CONTACT AREA
100u" TIN PLATING ON SOLDERTAILS
30u" NICKEL UNDERPLATING OVER ALL
PEG:100u" TIN PLATING ON SOLDERTAILS
30u" NICKEL UNDERPLATING OVER ALL



℄ OF DATUM B





RECOMMEND PCB LAYOUT
PCB TOLERANCE:±0.05





SECTION A-A





SECTION B-B

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

GENERAL TOLERANCES UNLESS SPECIFIED		深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
.X±0.30	.X°±3°	PART NO. HMT-SATA22M-S06C2	TITLE: SATA 7+15P 母座 SMT H:5.00 板下型侧插式	
.XX±0.20	.XX°±2°			
.XXX±0.05	.XXX°±0.5°	DESIGN: James	CUSTOMER	SIZE / UNITS: A4 / MM
MANUFACTURE DWG		CHED: Talen		SCALE / SHEET: N:A / 1/1
		APPD: Sophia		