








RoHS
Compliant
2011/65/EU





REV.	ECN NO OR DESCRIPTION	REVISED	DATE




SEE DETAIL:B
SCALE 2/1



SEE DETAIL:C
SCALE 2/1



吸嘴尺寸参考
NozzleDIM./Reference



UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	充电弹片 2.77xW1.34xH4.27 Shielding Clip,SMT			
DWN	xiong	PART NO.	TXTA-427BA-0220A	
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4




CUSTOMER COPY



RoHS
Compliant
2011/65/EU



REV.	ECN NO OR DESCRIPTION	REVISED	DATE



3D VIEW

NOTES:

(1)MATERIAL:

1-1:STAINLESS STEEL THICKNE=0.10mm

(2):FINISH:

2-1:REFER TO THE SPECIFICATION DESCRIPTION TABLE.

2-2:DIMENSIONS OF PCB PAD STENCIL ARE FOR REFERENCE ONLY, CUSTOMER CAN MODIFY IT BY THEIR OWN.

(3):PRODUCT SPECIFICATIONS:

3-1:RATED CURRENT:1.5A/MAX

3-2:VOLTAGE RATING:5.0V/AC/DC/MAX

3-3:CONTACT RESISTANCE:50mΩ/MAX

3-4:OPERATING TEMPERATURE:-40°C~85°C

3-5:NORMAL FORCE OF PRESS 0.57MM:0.28±0.1N.

3-6:DURABILITY:10,000 CYCLES.




(4):SALT SPRAY:48 HOURS(JUST BY ALL OUTSIDE AREA)

(5):PACKING SPECIFICATION:REEL&TARE

(6):DIMENSIONS MARKED ◻ ,CPK> 1.33

(7):ALL DIMENSIONS MARKED ▼ MUST BE CONTROLLED BY QC;

(8):COMPLIANT TO RoHS&LEAD FREE



RECOMMENDED PCB LAYOUT
TOLERANCE±0.05(焊盘推荐图)
(FOR REFERENCE ONLY)

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	充电弹片L2.77×W1.34×H4.27 Shielding Clip,SMT			
DWN	xiong	PART NO. TXTA-427BA-0220A		
CHKD	lee	SCALE:1:1	UNIT: mm	☉
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY