












A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		




NOTES:

- MECHANICAL: MATING FORCE: 5-20N .
UNMATING FORCE: 8-20N .
DURABILITY: 10000 CYCLES MIN.
- ELECTRICAL:
CURRENT: 3.0A/5.0A MAX
VOLTAGE: 20V MAX
WITHSTANDING VOLTAGE: 100V AC
CONTACT RESISTANCE: 40 mΩ MAX INITIAL;
50 mΩ MAX AFTER 10000 CYCLES
- ENVIRONMENTAL:
OPERATING TEMPERATURE RANGE -30° C ~ +80° C
- Salt Spray: 24H


BOM

序号	名称	材料规格
1	Terminal	C2680 TM02 T=0.15mm 电镀全金 Au:GF Ni:50u"
2	Terminal	C2680 TM02 T=0.15mm 电镀全金 Au:GF Ni:50u"
3	Molding 1	LCP+30%G.F黑色 UL94 V-0
4	Molding 2	LCP+30%G.F黑色 UL94 V-0
5	Molding 3	LCP+30%G.F黑色 UL94 V-0
6	Shell	SUS201 1/2H T=0.30mm Ni:50u"

X. ±0.50	X° ± 2°	UNITS mm	广东创粤科技有限公司						
.X ±0.30	.X° ± 1°								
.XX ±0.10	.XX° ± 0.5°	MAT'L /	TITLE:						
.XXX ± 0.05			TYPE-C 16PIN板上四脚插板SMT母座 长L=7.35MM 无弹 3MD						
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD		FINISH /	TYPE-C-16P-L7.35SMT-31435		DWG NO.:				
			CHKD:						
		Q'TY /	DR:				SCALE	SHEET	REV.
							1/1	1/1	A1

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

SCALE	SHEET	REV.
1/1	1/1	A1



REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		

