




REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		



RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED $\pm 0.05\text{mm}$

NOTES:

- MECHANICAL: MATING FORCE: 5-20N .
UNMATING FORCE: 8-20N .
DURABILITY: 10000 CYCLES MIN.
- ELECTRICAL:
CURRENT: 3.0A MAX
VOLTAGE: 20V MAX
WITHSTANDING VOLTAGE: 100V AC
CONTACT RESISTANCE: 40 m Ω MAX INITIAL;
50 m Ω MAX AFTER 10000 CYCLES
- ENVIRONMENTAL:
OPERATING TEMPERATURE RANGE -30° C ~ +80° C
- Salt Spray: 24H

BOM		
序号	名称	材料规格
1	Terminal	C2680 T=0.15mm 电镀金1u" Ni:50u"
2	卡勾	SUS301 3/4H T=0.15mm 素材
3	Molding 3	LCP 黑色 UL94 V-0
4	Shell	SUS201 1/4H T=0.30mm Ni:50u"


广东创粤科技有限公司

TITLE:
TYPE-C 16PIN沉板1.0MM母座 长L=6.50MM

TYPE-C-16P-R1.0L6.5-34008 DWG NO.:

CHKD:

DR:



SCALE SHEET REV.
1/1 1/1 A1

A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND
PIN	SIGNAL NAME	PIN	SIGNAL NAME

X.	± 0.50	X.*	$\pm 2^{\circ}$
.X	± 0.30	.X*	$\pm 1^{\circ}$
.XX	± 0.10	.XX*	$\pm 0.5^{\circ}$
.XXX	± 0.05		






THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD

UNITS
mm

MAT'L


FINISH

Q'TY







REV.	ZONE	DESCRIPTION	DESIGN	DATE
B		NEW		




24.00±0.3



ADHESIVE TAPE


PULL OUT DIRECTION



Ø330

30.0

1000PCS/每卷



10卷/每箱

X. ±0.50	X.° ± 2°	UNITS mm	广东创粤科技有限公司	
.X ±0.30	.X° ± 1°	MAT'L	TITLE:	
.XX ±0.10	.XX° ± 0.5°		TYPE-C 16PIN沉板1.0MM母座 长L=6.50MM	
.XXX ± 0.05		FINISH	TYPE-C-16P-R1.0L6.5-34008	DWG NO.:
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD.			CHKD:	SCALE SHEET REV.
			Q'TY	1/1 1/1 A1
			DR:	