




SPECIFICATION:

1. MATERIAL:

HOUSING: LCP UL 94V-0

COLOR:BLACK

CONTACT: PHOSPHOR BRONZE C5191R-H, T=0.25mm

PEG: BRASS C2680R-H, T=0.30mm

2. FINISH:

CONTACT:1u"/3u"/5u"/15u" GOLD PLATING ON CONTACT AREA

100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL

PEG:100u" TIN PLATING ON SOLDERTAILS

30u" NICKEL UNDERPLATING OVER ALL

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Pho. Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
GENERAL TOLERANCES UNLESS SPECIFIED		HMTCONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
.X±0.30	.X°±3°	PART NO.	TITLE: SATA 7+15P 母座	
.XX±0.20	.XX°±2°	HMT-SATA22M-S05C2	SMT H:4.20 板下型 侧插式	
.XXX±0.05	.XXX°±0.5°	DESIGN: James	CUSTOMER	SIZE
MANUFACTURE DWG		CHED: Talen		UNITS
		APPD: Sophia		SCALE
				SHEET
			N:A	1/1