











RoHS
Compliant
2011/65/EU



REV.	ECN NO OR DESCRIPTION	REVISED	DATE



DETAIL:B
SCALE 2:1



DETAIL:C
SCALE 2:1

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10






东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	充电弹片L2.97×1.34×H3.67 charging contact spring			
DWN	xiong	PART NO.	TXTA-367BA-0050A	
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4



CUSTOMER COPY



耳机插入示意图(仅供参考)



耳机插入力曲线图(仅供参考)



RECOMMENDED PCB LAYOUT
TOLERANCE±0.05(焊盘推荐图)
(FOR REFERENCE ONLY)

- NOTES:
- 1:MATERIAL:
1-1:STAINLESS STEEL THICKNE=0.08±0.03mm
- 2:FINISH:
2-1:REFER TO THE SPECIFICATION DESCRIPTION TABLE.
2-2:DIMENSIONS OF PCB PAD STENCIL
ARE FOR REFERENCE ONLY,
CUSTOMER CAN MODIFY IT BY THEIR OWN.
- 3:PRODUCT SPECIFICATIONS:
3-1:RATED CURRENT:1.5A/MAX
3-2:VOLTAGE RATING:5.0V/AC/DC/MAX
3-3:CONTACT RESISTANCE:50mΩ/MAX
3-5:OPERATING TEMPERATURE:-40°C~85°C
3-6:NORMAL FORCE OF PRESS@0.50:18gf±8gf.
3-7:DURABILITY:10,000 CYCLES.
- 4:SALT SPRAY:48 HOURS(JUDGED BY ALL OUTSIDE AREA)
- 5:PACKING SPECIFICATION:REEL&TARE
- 6:DIMENSIONS MARKED ▣,CPK>1.33
- 7:ALL DIMENSIONS MARKED ▼ MUST BE CONTROLLED BY QC;
- 8:COMPLIANT TO RoHS&LEAD FREE

UNLESS OTHERWISE SPECIFIED TOLERANCES		 东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD				
DECIMALS: ANGLES:		TITLE 充电弹片 L2.97×1.34×H3.67 charging contact spring				
X :±0.30	X :±2°	DWN	xiong	PART NO. TXTA-367BA-0050A		
X.X :±0.20	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm	
X.XX :±0.10		APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4
		CUSTOMER COPY				