




SPECIFICATION:

1. MATERIAL:

HOUSING:LCP 30% G/F UL 94V-0

COLOR:BLACK

CONTACT:BRASS C2680R-H, T=0.25mm

PEG: BRASS C2680R-H, T=0.30mm

2. FINISH:

CONTACT:1u", 3u", 5u", 15u"GOLD PLATING ON CONTACT AREA

100u" MIN. TIN PLATING ON SOLDER TAILS

40u" MIN. NICKEL UNDERPLATING OVER ALL

3. ELECTRICAL:

CURRENT RATING:1.5 AMPERE PER CONTACT


CONTACT RESISTANCE:30 MILLIOHMS MAX

INSULATION RESISTANCE:1000 MEGOHMS MIN

DIELECTRIC WITH STANDING VOLTAGE:500 VDC

OPERATING TEMPERATURE: -40° C ~ +85° C

4. THE MARK (XX) DIMENSIONS MUST BE MEASURED BY FAI.

| 环保要求                                   |             | 产品必须符合ROHS要求                                                                                                                                                                      |                                                                                       |                 |
|----------------------------------------|-------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-----------------|
| 3                                      | Peg         | Brass C2680                                                                                                                                                                       |                                                                                       | Tin/Ni Plated   |
| 2                                      | Terminal    | Brass C2680                                                                                                                                                                       |                                                                                       | Gold/Tin Plated |
| 1                                      | Housing     | High Temp                                                                                                                                                                         | Black                                                                                 | UL 94V-0        |
| NO.                                    | DESCRIPTION | MATERIAL                                                                                                                                                                          | COLOR                                                                                 | REMARK          |
| GENERAL TOLERANCES<br>UNLESS SPECIFIED |             | <div> 深圳市华明通电子有限公司</div> <div><b>HMTCONN</b> Shenzhen Huamingtong Electronics Co., Ltd</div> |                                                                                       |                 |
| .X±0.30                                | .X°±3°      | PART NO.<br>HMT-SATA22G-S08                                                                                                                                                       | TITLE: SATA7+15P公座沉板式<br>SMT HO.9 (半包式)                                               |                 |
| .XX±0.20                               | .XX°±2°     |                                                                                                                                                                                   |                                                                                       |                 |
| .XXX±0.05                              | .XXX°±0.5°  | DESIGN: James                                                                                                                                                                     | CUSTOMER                                                                              | SIZE            |
| MANUFACTURE DWG                        |             | CHED: Talen                                                                                                                                                                       |                                                                                       | UNITS           |
|                                        |             | APPD: Sophia                                                                                                                                                                      |  | MM              |
|                                        |             |                                                                                                                                                                                   |                                                                                       | SCALE           |
|                                        |             |                                                                                                                                                                                   |                                                                                       | SHEET           |
|                                        |             |                                                                                                                                                                                   |                                                                                       | N:A             |
|                                        |             |                                                                                                                                                                                   |                                                                                       | 1/1             |