










RoHS  
Compliant




| REV. | ZONE | DESCRIPTION | DESIGN | DATE |
|------|------|-------------|--------|------|
| B    |      | NEW         |        |      |




- NOTES:
1. MECHANICAL: MATING FORCE: 5-20N .  
UNMATING FORCE: 8-20N .  
DURABILITY: 10000 CYCLES MIN.
2. ELECTRICAL:  
CURRENT: 5.0A MAX  
VOLTAGE: 20V MAX  
WITHSTANDING VOLTAGE: 100V AC  
CONTACT RESISTANCE: 40 mΩ MAX INITIAL;  
50 mΩ MAX AFTER 10000 CYCLES
3. ENVIRONMENTAL:  
OPERATING TEMPERATURE RANGE -30° C ~ +80° C
4. Salt Spray: 48H



|     |             |     |             |
|-----|-------------|-----|-------------|
| A1  | GND         | B12 | GND         |
| A4  | VBUS        | B9  | VBUS        |
| A5  | CC1         | B8  | SBU2        |
| A6  | DP1         | B7  | DN2         |
| A7  | DN1         | B6  | DP2         |
| A8  | SBU1        | B5  | CC2         |
| A9  | VBUS        | B4  | VBUS        |
| A12 | GND         | B1  | GND         |
| PIN | SIGNAL NAME | PIN | SIGNAL NAME |

|                                                                                                                                                                                                                                      |             |             |                                              |                           |     |          |                                                                                       |       |       |
|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------|-------------|----------------------------------------------|---------------------------|-----|----------|---------------------------------------------------------------------------------------|-------|-------|
| X. ±0.50                                                                                                                                                                                                                             | X.° ± 2°    | UNITS<br>mm | 广东创粤科技有限公司                                   |                           |     |          |                                                                                       |       |       |
| .X ±0.30                                                                                                                                                                                                                             | .X° ± 1°    |             |                                              |                           |     |          |                                                                                       |       |       |
| .XX ±0.10                                                                                                                                                                                                                            | .XX° ± 0.5° | MAT'L       | TITLE:<br><br>TYPE-C 16PIN板上母座 前插后贴 L=7.35MM |                           |     |          |                                                                                       |       |       |
| .XXX ± 0.05                                                                                                                                                                                                                          |             |             |                                              |                           |     |          |                                                                                       |       |       |
| THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD |             |             | FINISH                                       | TYPE-C-16P-L7.35SMT-31437 |     | DWG NO.: |                                                                                       |       |       |
|                                                                                                                                                                                                                                      |             |             | Q'TY                                         | CHKD:                     |     |          |                                                                                       |       |       |
|                                                                                                                                                                                                                                      |             |             |                                              |                           | DR: |          |  | SCALE | SHEET |
|                                                                                                                                                                                                                                      |             |             |                                              |                           |     | 1/1      |                                                                                       | 1/1   | A1    |



| REV. | ZONE | DESCRIPTION | DESIGN | DATE |
|------|------|-------------|--------|------|
| B    |      | NEW         |        |      |

A

B

C

D

E

SMT端子方向

圆孔间距

4.00

1.75

W=24.00

12.00

客户拉出方向

自粘上带(上带剥离力0.2-1.2N)

前端

产品内标签

产品标签格式(所有包装格式一致,只需更改数量即可)

包装示意图:

后空19PCS

1000 P C S

前空19PCS

产品放置区

ø100

ø330

28.2Ref

卷带盘10盘

10盘

将10盘产品放入纸箱内

产品外标签

备注:

- 1.把上下载带送入载带机进行调整,然后将产品按照指定的方式摆入下载带中,开动卷带机进行卷装(每卷包1000PCS),卷装完成后需用上带缠绕最少19CM;
- 2.在卷装OK的每卷盘面的指定位置上贴上物料和RoHS标签装入纸箱内,每箱装10盘
- 3.纸箱用封箱带将其封好,胶带要求工字型,不可遮住标签;
- 4.如果客户对包装标签另有要求,请按客户要求作业;有未满足之零数箱需用缓冲材料填充;
- 5.上载带剥离力 0.2-1.2N.;

纸箱规格:  
34.0X34.0X30.5CM

|                                                                                                                                                                                                                                       |        |      |        |             |            |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------|------|--------|-------------|------------|
| X.                                                                                                                                                                                                                                    | ± 0.50 | X.°  | ± 2°   | UNITS<br>mm | 广东创粤科技有限公司 |
| .X                                                                                                                                                                                                                                    | ± 0.30 | .X°  | ± 1°   |             |            |
| .XX                                                                                                                                                                                                                                   | ± 0.10 | .XX° | ± 0.5° | MAT'L       |            |
| .XXX                                                                                                                                                                                                                                  | ± 0.05 |      |        | FINISH      |            |
| THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF GUANGDONG CHUANGYUE TECHNOLOGY CO.,LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF GUANGDONG CHUANGYUE TECHNOLOGY CO., LTD. |        |      |        | Q'TY        |            |

TITLE:


TYPE-C 16PIN板上母座 前插后贴 L=7.35MM

APPD:

CHKD:

DR:

DWG NO.:



| SCALE | SHEET | REV. |
|-------|-------|------|
| 1/1   | 1/1   | A1   |