






A







RECOMMENDED ASSEMBLY



B



C



G-Switch USB-C Specification:

- Current rated: 5A on vbus/1.25A on vconn/0.25A on other
- Voltage rating: 24V AC
- Withstanding voltage: 100V AC/minute
- Contact resistance: 40mΩ Max
- Insulation resistance: 100MΩ Min
- Operating temperature: -40°C ~ +85°C
- Mating force: 5N~20N
- Unmating force: 8N~20N
- Durability cycle: 10,000 cycles
- Waterproof grade: IP-X6.


A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND			VBUS	CC1	D+	D-	SBU1	VBUS			GND
First			First	Second	Second	Second	Second	First			First

B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
GND			VBUS	SBU2	D-	D+	CC2	VBUS			GND
First			First	Second	Second	Second	Second	First			First

D

NO.	PARTS	MATERIAL	REMARKS
1	SHELL	ZINC ALLOY	Ni50u" PLATED
2	GND PLATE	STAINLESS STEEL316	—
3	MID PLATE	STAINLESS STEEL301	—
4	HOUSING	HIGH TEMPERATURE PLASTIC	PA9T BLACK UL 94 V-0
5	TERMINALS	COPPER ALLOY C7025	Au3u" PLATING ON CONTACT AREA TiIn50u" PLATING ON SOLDER AREA
6	RUBBER	SILICA GEL	RED

PCB REFERENCE DIAGRAM TOLERANCE:±0.05



SCALE: 1:1 UNIT: mm
SIZE: A4

Unless otherwise
General Tolerance:
X. ±0.40
X.x ±0.30
X.xxx ±0.20
X.xxxx ±0.10
X° ±5°

Title: Horizontal Type-c 16P Female SMT
Mid-Mount0.8 CH=0.78 L=6.7mm

Molde Code: GT-USB-7103A03

DRAWN	CHECKED	APPROVED	DATE
Xia	Chen	Chen	2024.12.11

品赞科技
b-Switch
www.dg-switch.com

REV: A0 SHEET: 1/1

E

A

B

C

D

E