





| 序号 | 品名                                                              | 材质                                   |
|----|-----------------------------------------------------------------|--------------------------------------|
| ①  | 4.2A型双排立式WTB胶芯<br>4.2A Type Double-row<br>Vertical WTB Housing  | LCP UL94V-0 黑色<br>LCP UL94V-0 Black  |
| ②  | 4.2A型双排立式WTB端子<br>4.2A Type Double-row<br>Vertical WTB Terminal | 铜合金/表面镀锡<br>Copper Alloy/Tin Plating |

- 技术指标:
1. 工作温度(Temperature range): -25° C~85° C.
  2. 额定电压(Rated voltage): 250V AC, DC.
  3. 耐电压(Dielectricwithstanding voltage): 1500V AC/minute.
  4. 接触电阻(Contact Resistance) 20mΩ.
  5. 绝缘电阻(Insulation resistance): ≥1000MΩ.
  6. 额定电流(Rated voltage): 5A AC, DC.

| Part No         | CKT  | A     | B     | C     |
|-----------------|------|-------|-------|-------|
| WF-5557-BS2PL2  | 2X2  | 4.20  | 9.60  | 0.00  |
| WF-5557-BS3PL2  | 2X3  | 8.40  | 13.80 | 4.20  |
| WF-5557-BS4PL2  | 2X4  | 12.60 | 18.00 | 8.40  |
| WF-5557-BS5PL2  | 2X5  | 16.80 | 22.20 | 12.60 |
| WF-5557-BS6PL2  | 2X6  | 21.00 | 26.40 | 16.80 |
| WF-5557-BS7PL2  | 2X7  | 25.20 | 30.60 | 21.00 |
| WF-5557-BS8PL2  | 2X8  | 29.40 | 34.80 | 25.20 |
| WF-5557-BS9PL2  | 2X9  | 33.60 | 39.00 | 29.40 |
| WF-5557-BS10PL2 | 2X10 | 37.80 | 43.20 | 33.60 |
| WF-5557-BS11PL2 | 2X11 | 42.00 | 47.40 | 37.80 |
| WF-5557-BS12PL2 | 2X12 | 46.20 | 51.60 | 42.00 |

| GENERAL TOLERANCES<br>UNLESS SPECIFIED |     | PART NO.<br>WF-5557-BSNPL2 |        | TITLE:<br>4.2A型双排立式WTB业务图 |       |
|----------------------------------------|-----|----------------------------|--------|---------------------------|-------|
| X.±0.50                                | ±1° | DESIGN:                    | James  | CUSTOMER                  | SIZE  |
| X.X±0.20                               |     | CHED:                      | Talen  |                           | A4    |
| X.XX±0.10                              |     | APPD:                      | Sophia |                           | UNITS |
| MANUFACTURE DWG                        |     |                            |        | SCALE                     | SHEET |
|                                        |     |                            |        | N:A                       | 1/2   |



|                                        |     |                                                                                                                          |                           |              |
|----------------------------------------|-----|--------------------------------------------------------------------------------------------------------------------------|---------------------------|--------------|
| GENERAL TOLERANCES<br>UNLESS SPECIFIED |     | <div><div><div></div><div>HMTCONN</div></div><div>深圳市华明通电子有限公司<br/>Shenzhen Huamingtong Electronics Co., Ltd</div></div> |                           |              |
| X.±0.50                                | ±1° | PART NO.<br>WF-5557-BSNPL2                                                                                               | TITLE:<br>4.2A型双排立式WTB业务图 |              |
| X.X±0.20                               |     |                                                                                                                          |                           |              |
| X.XX±0.10                              |     | DESIGN: James                                                                                                            | CUSTOMER                  | SIZE<br>A4   |
| MANUFACTURE DWG                        |     | CHED: Talen                                                                                                              |                           | UNITS<br>MM  |
|                                        |     | APPD: Sophia                                                                                                             |                           | SCALE<br>N:A |
|                                        |     |                                                                                                                          |                           | SHEET<br>2/2 |