








REV.	ECN NO OR DESCRIPTION	REVISED	DATE











RECOMMENDED PCB LAYOUT
TOLERANCE±0.05(焊盘推荐图)
(FOR REFERENCE ONLY)



- NOTES:
1:MATERIAL:
1-1:COPPER ALLOY THICKNE=0.10mm
2:FINISH:
2-1:SEE DETAILED LIST.
3:PRODUCT SPECIFICATIONS:
3-1:RATED CURRENT:1.5A/MAX
3-2:VOLTAGE RATING:5.00V/AC/DC/MAX
3-3:CONTACT RESISTANCE:50mΩ/MAX
3-4:OPERATING TEMPERATURE:-40°C~85°C
3-5:NORMAL FORCE OF PRESS@0.55mm:20g±10g.
3-6:DURABILITY:10,000 CYCLES.
4:SALT SPRAY:SEE DETAILED LIST.
5:PACKING SPECIFICATION:REEL&TARE
6:DIMENSIONS MARKED ◻ ,CPK>1.33
7:ALL DIMENSIONS MARKED ▼ MUST BE CONTROLLED BY QC;
8:COMPLIANT TO RoHS&LEAD FREE
9:PART NO.;



UNLESS OTHERWISE SPECIFIED TOLERANCES		 东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD				
DECIMALS: ANGLES:		TITLE 充电弹片L3.00×W1.50×H6.70Shielding Clip,SMT				
X :±0.30	X :±2°	DWN	xiong	PART NO. TXTA-670B5-0069A		
X.X :±0.20	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm	
X.XX :±0.10		APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4
		CUSTOMER COPY				



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

UNLESS OTHERWISE SPECIFIED TOLERANCES		东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD				
DECIMALS:	ANGLES:	TITLE	充电弹片L3.00×W1.50×H6.70 Shielding Clip,SMT			
X :±0.30	X :±2°	DWN	xiong	PART NO. TXTA-670B5-0069A		
X.X :±0.20	X.X :±1°	CHKD	lee	SCALE:1:1	UNIT: mm	
X.XX :±0.10		APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4
		CUSTOMER COPY				