




SPECIFICATION:
1. MATERIAL:
HOUSING: LCP 30% G/F UL 94V-0
COLOR: BLACK
CONTACT: PHOSPHOR BRONZE C5191R-H, T=0.25mm
PEG: BRASS C2680R-H, T=0.30mm
2. FINISH:
CONTACT: 1u" GOLD PLATING ON CONTACT AREA
100u" TIN PLATING ON SOLDER TAILS
30u" NICKEL UNDERPLATING OVER ALL
PEG: 100u" TIN PLATING ON SOLDER TAILS
30u" NICKEL UNDERPLATING OVER ALL

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Pho. Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
GENERAL TOLERANCES UNLESS SPECIFIED		HMTCONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd		
.X±0.30	.X°±3°	PART NO.	TITLE: SATA 7+15P 母座 板下SMT H7.50鱼叉侧插式	
.XX±0.20	.XX°±2°	HMT-SATA22M-S04C2	CUSTOMER	SIZE
.XXX±0.05	.XXX°±0.5°	DESIGN: James		UNITS
MANUFACTURE DWG		CHED: Talen	SCALE	SHEET
		APPD: Sophia		1/1