



NOTES:

备注

- 1.Brass or purple copper,tin-plating
黄铜, 镀锡
- 2.Wire screw hole M4 (M3,M5)
压线螺孔M4 (M3, M5) 可定制
- 3.Current Rating: 60A
额定电流:60A
- 4.There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
- 5.Unmarked dimensions refer to tolerances
未标注的尺寸参考公差
- 6.扭矩: 1.47 Nm

Ordering Information

HC - * ** * - **** - D *** * - 07

Type	Thickness	Screw Thread	Welding Feet	Series	D=0.1P	Product No.	Material
Full Teeth (插牙)	0.8mm	M4	0.8mm	0808	S=0.1P	默认	Copper
Rivet Nut (铆螺母)	1.2mm	M4	1.2mm	1208	S=0.1P	产品序号	紫铜
Rivet Gasket (铆垫片)	1.5mm	M4	1.5mm	1508	S=0.1P		紫铜
	2.0mm	M4	2.0mm	2008	S=0.1P		
	2.5mm	M4	2.5mm	2508	S=0.1P		
	3.0mm	M4	3.0mm	3008	S=0.1P		
	3.2mm	M4	3.2mm	3208	S=0.1P		

GENERAL TOLERANCE		制图	07	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
DIM TOL		审核		产品名称	PCB 焊接端子 厚度1.0 插板 抽牙	版本	A
5 or more ±0.35		批准		TITLE	M4 4焊脚 8x8x27mm	REV.	
2~5 ±0.25		比例		产品料号	HC-M1044-0808-D333-07	单位	mm
0~2 ±0.15		投影		PART NO.		页次	1/1
Angle ±3.0°		Projection		MATERIAL		SHEET	