









SPECIFICATION

1. Rating : DC 12V 50mA.
2. Function: 1P2T
3. Contact resistance: $\leq 100\text{m}\Omega$.
4. Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V).
5. Withstanding voltage: 250VAC .
6. Operating Force: $160\pm 50\text{gf}$
7. life test: 10000 cycles.
8. Travel: $1.2\pm 0.1\text{mm}$.
9. Operation temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$
10. Sign "*" is importance dimension.

电话 : 0769-82310511-867
邮箱 : hooya89@hooya.hk

CIRCUIT DIAGRAM



P.C.B MOUNTING PATTERN DIMENSION

the following soldering are recommended
for reflow soldering

					TOLERANCE UNLESS SPECIFIED							
6	TERMINAL	PHOSPHOR BRONZE	1	AG-PLATED	<1.5: $\pm 0.1\text{mm}$	ANGULAR	A0	2025.03.25	首次发行		LP	
5	CASE	LCP	1		>1.5~5.0: $\pm 0.25\text{mm}$	$\pm 1^{\circ}$	NO	DATE	REVISIONS		BY	APPD
4	CONTACT	SUS	1		>5.0: $\pm 0.3\text{mm}$							
3	SPRING PLATE	Be-CU	1	AG-PLATED	TITLE: MINI SLIDE SWITCH		UNIT : MM		ROHS	DWN		
2	STEM	PPA	1		MODEL: MK-12C03G1.5-B-07		SCALE: 1:1		COMPLIANT	CHK'D		
1	COVER	BRASS	1	AG-PLATED						APPD		
NO.	PART	NAME	MATERIAL	QTY	FINISHING					PRO.AGL:		REV :A0



DONGGUANG HAOYU ELECTRONICS CO., LTD
皓宇 东莞市弘皓电子有限公司

PRO.AGL: