






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.11.03	
/	N/A		/	/	/



26.00 [1.024]




M3



PCB LAYOUT

B-B

1.00~3.00mm






KHV-220 W V-M6 A S

M6:M6

A:A
B:B
C:C
B:
S:

- Specifications()
- 1.Voltage rating():1000V DC
 - 2.Current rating():120A
 - 3.Withstanding voltage():3000V AC 1Min, 2mA MAX
 - 4.Insulation resistance():200MQ MIN at DC500V
 - 5.Protection level():IP67
 - 6.Mating cycles 100 cycles Min
 - 7.Recommended screw torque():
M3: 0.8~1.2N.m
M6: 4.5~5.5N.m
 - 8.Temperature range():-40 ~+125



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE: 2
CHECKED		UNIT: mm/in	PART NO.: KHV-220WV-M6AS
APPROVED		SIZE: A4	DWG NO.: