











SPECIFICATION

1. Rating : DC12V 0.1A.
2. Contact resistance: $\leq 100\text{m}\Omega$.
3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC500V).
4. Withstanding voltage: 500VAC .
5. Operating Force: $1\pm 0.5\text{N}$.
6. life test: 10,000 cycles.
7. Operation temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
8. Sign"* "is importance dimension.

电话 : 0769-82310511-867

邮箱 : hooya89@hooya.hk

防水等级 : IP67

8					TOLERANCE UNLESS SPECIFIED											
7	TERMINAL	BRASS	2	Ag-PLATED												
6	REED	PHOSPHOR BRONZE	1	Ag-PLATED	<1.5: ±0.1mm	ANGULAR										
5	SPRING	STEEL WIRE	1		>1.5~5.0: ±0.25mm	±1°										
					>5.0: ±0.3mm		NO	DATE	REVISIONS			BY	APPD			
4	HOUSING	PBT	1	BLACK	TITLE: MICRO SWITCH				UNIT : MM	ROHS	DWN					
3	WATERPROOF HAT	PC	1	GRAY	MODEL:RTM3-00N-NO-100-GY-08				SCALE: 1:1	COMPLIANT	CHK'D					
2	BUTTON	POM	1	BLACK	东莞市六钧电子五金有限公司								APPD			
1	COVER	PBT	1	BLACK												
NO.	PART	NAME	MATERIAL	QTY	FINISHING								PRO.AGL:			REV :A0