










NOTES:
CHAMFER EDGE MUST BE FREE OF CUTTING BURRS



POS.	DIM. A	DIM. H	"M"
36	6	8.15	B17
64	20	22.15	B31
98	37	39.15	B48
164	70	72.15	B81

				TOLERANCE		UMax 东莞市友贸实业有限公司 conn DONGGUAN UMAX ENTERPRISE LIMITED		TITLE: PCI EXPRESS 4.0 SMT TYPE					
				LINEAR	ANGLES			PART NO. PCIE-G405XXXXX					
				X.±	X'.±			DWG NO. C-PCIE-G405					
	See Sheet 1			.XX±	.XX'±	APPD: Jason	MAT'L:		UNITS	SCALE	SHEET	REV	
REV	ECN NO.	NAME	DATE	.XXX±	.XXX'±	CHKD: Schumi	FINISH:		MM	1 : 1	2 OF 4	A2	
2		3		4		5		6		7		8 CUSTOMER	



RECOMMENDED PCB LAYOUT
(COMPONENT SIDE)
TOLERANCE: ± 0.05

POS.	DIM. A	DIM. J	DIM. K	"M"
36	6	9.15	28.0	B17
64	20	23.15	42.0	B31
98	37	40.15	59.0	B48
164	70	73.15	92.0	B81

				TOLERANCE		UMax conn 东莞市友贸实业有限公司 DONGGUAN UMAX ENTERPRISE LIMITED		TITLE: PCI EXPRESS 4.0 SMT TYPE				
				LINEAR	ANGLES			PART NO. PCIE-G405XXXXX				
				X.±	X'.±							
				.X±	.X'±							
	See Sheet 1			.XX±	.XX'±	APPD: Jason	MAT'L:		UNITS	SCALE	SHEET	REV
REV	ECN NO.	NAME	DATE	.XXX±	.XXX'±	CHKD: Schumi	FINISH:					
						DRWN: Lei Songping	Q'TY:		MM	1 : 1	3 OF 4	A2

NOTES:

1. MATERIAL:

- 1.1 HOUSING: THERMOPLASTIC, HIGH TEMP, UL94V-0, COLOR: BLACK.
1.2 CONTACTS: COPPER ALLOY.
1.3 HOLDDOWN: COPPER ALLOY.
1.4 CAP: THERMOPLASTIC, HIGH TEMP, UL94V-0, COLOR: BLACK.

2. FINISH:

2.1 CONTACT:


SELECTIVE GOLD PLATING ON THE CONTACT AREA.
100μ" MIN. MATTE-TIN PLATING ON THE SOLDER TAILS,
50μ" MIN. NICKEL UNDERPLATING OVERALL.

2.2 HOLDDOWN:


100μ" MIN. MATTE-TIN PLATING WITH 50μ" MIN. NICKEL UNDERPLATE OVERALL.

4. PRODUCT SPEC: PS-GEN4-01

5. PACKAGING SPEC: 311304001 FOR TRAY, 311304002 FOR REEL, 311304003 FOR HARD TRAY



WITH CAP



WITH MYLAR

PART NO.

PCIE-G405 1 X X X XX

HSG Color
1: Black

Contact Plating
0: 30u" Gold
1: 15u" Gold

No. of Pins
0: 36P
1: 64P
2: 98P
3: 164P


Halogen Options
Blank: Halogen
HF: Halogen Free

Packaging Options
T: Tray Packaging
C: Tray Packaging With Cap
N: Tray Packaging With Mylar
R: Tape & Reel Packaging
P: Tape & Reel Packaging With Cap
M: Tape & Reel Packaging With Mylar
A: 72mm Width Tape & Reel Packaging With Cap
Y: Hard Tray Packaging
Z: Hard Tray Packaging With Mylar
B: Hard Tray Packaging With Cap

	See Sheet 1		
REV	ECN NO.	NAME	DATE

TOLERANCE	
LINEAR	ANGLES
X.±	X'.±
.X±	.X'±
.XX±	.XX'±
.XXX±	.XXX'±

UMax 东莞市友贸实业有限公司 conn DONGGUAN UMAX ENTERPRISE LIMITED		APPD: Jason	MAT'L:
		CHKD: Schumi	FINISH:
		DRWN: Lei Songping	Q'TY:

TITLE: PCI EXPRESS 4.0 SMT TYPE				
PART NO. PCIE-G405XXXXX				
DWG NO. C-PCIE-G405				
	UNITS	SCALE	SHEET	REV
	MM	1 : 1	4 OF 4	A2

CUSTOMER