





1. Rating : DC12V 0.1A.
2. Contact resistance: $\leq 500\text{m}\Omega$.
3. Insulation resistance: $\geq 100\text{M}\Omega$ (DC250V).
4. Withstanding voltage: 250VAC .
5. Operating Force: $1\pm 0.4\text{N}$.
6. life test: 300,000 cycles.
7. Operation temperature range: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
8. Sign"* "is importance dimension.

8					TOLERANCE UNLESS SPECIFIED												
7	TERMINAL	BRASS	2	Ag-PLATED													
6	REED	PHOSPHOR BRONZE	1	Ag-PLATED	<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°											
5	SPRING	STEEL WIRE	1				NO	DATE	REVISIONS		BY	APPD					
4	HOUSING	PBT	1	BLACK	TITLE: MICRO SWITCH			UNIT : MM		ROHS COMPLIANT	DWN						
3	WATERPROOF SLEEVE	PC	1	GRAY	MODEL:RTM3-00P-N0-100-GY-E-08			SCALE: 1:1			CHK'D						
2	BUTTON	POM	1	BLACK	东莞市六钧电子五金有限公司									APPD			
1	COVER	PBT	1	BLACK													
NO.	PART NAME	MATERIAL	QTY	FINISHING										PRO.AGL:			REV :AC