

3-Ampere, 50-1000 Voltage Surface Mount High Efficiency Silicon Rectifiers


■ Features

- Glass passivated chip
- Low reverse leakage current
- Super fast reverse recovery time
- High surge current capability
- Low switching losses and high efficiency
- The plastic case material has UL flammability classification rating 94V-0

Key Parameters		
Parameter	Value	Unit
I_F	3	A
V_{RRM}	50~1000	V
I_{FSM}	100	A
Package	SMB	

■ Mechanical Data

- Package: SMB
- Polarity: As marked
- Lead free complies with the EU ROHS directive
- Terminals: Tin plated leads, solderable per Mil-STD-750 Method 2026



■ Typical applications

- For use in general purpose rectification of power supplies, inverters, converters and freewheeling diodes for consumer, and telecommunication.

■ Maximum Ratings @ $T_a = 25^\circ\text{C}$ unless otherwise noted

PARAMETER		SYMBOL	US3AB	US3BB	US3DB	US3GB	US3JB	US3KB	US3MB	UNIT
Maximum recurrent peak reverse voltage		V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage		V _{RSM}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage		V _{DC}	50	100	200	400	600	800	1000	V
Maximum average forward rectified current at T _L =100°C		I _{FM}	3							A
Maximum instantaneous forward voltage @I _F =I _{FM}		V _F	1.0			1.3		1.7		V
Forward Surge Current (Non-repetitive) @ 60Hz Half-sine wave,1 cycle, T _j =25°C		I _{FSM}	100							A
Maximum Reverse recovery time @I _F =0.5A ,I _R =1A ,I _{rr} =0.25A		T _{RR}	50				75			nS
Junction temperature range		T _j	-55~+150							°C
Storage temperature range		T _{STG}	-55~+150							°C
Maximum DC reverse current at rated DC blocking voltage	T _j =25°C	I _R	5							μA
	T _j =100°C		200							μA

Characteristic Curve




FIG1. Forward Current Derating Curve




FIG2. Maximum Non-Repetitive Peak Forward Surge Current




FIG3. Typical Forward Voltage Characteristics






FIG4. Typical Reverse Characteristics

■ Package Outline Dimensions (SMB/DO-214AA)

	Symbol	Dimensions			
		Millimeters		Inches	
		Min.	Max.	Min.	Max.
	A	1.85	2.21	0.073	0.087
	B	4.25	4.85	0.167	0.191
	C	3.30	3.94	0.130	0.155
	D	2.15	2.65	0.085	0.104
	E	0.75	1.52	0.030	0.060
	F	-	0.203	-	0.08
	G	5.08	5.59	0.200	0.220
	H	0.15	0.31	0.006	0.012

■ Suggested Pad Layout

	Symbol	Reference Dimensions	
		Millimeters	Inches
	A	2.30	0.091
	B	2.10	0.085
	C	2.70	0.106

■ Ordering Information

Package	Reel Size	Reel(pcs)	Identification
SMB	13"	3000	

Notice

XILONG reserves the right to make modifications,enhancements,improvements,corrections or other changes without further notice to any product herein. xilong does not assume any liability arising out of the application or use of any product described herein.