








SCHEMATIC



P.C.B LAYOUT



SPECIFICATION

- 1.Rating : DC12V 50mA.
- 2.Contact resistance: $\leq 100m\Omega$.
- 3.Insulation resistance: $\geq 100M\Omega$ (DC100V).
- 4.Withstanding voltage: 250VAC .
- 5.Operating Force: 300 $\pm$ 80gf.
- 6.Travel: 0.75 $\pm$ 0.2mm.
- 7.Life test: 100,000 cycles.
- 8.Operation temperature range: -25 $^{\circ}$ C~85 $^{\circ}$ C.

.防水等级: IP67

邮箱: hooya89@hooya.hk

电话: 0769-82310511-867

7					TOLERANCE UNLESS SPECIFIED								
6	TERMINAL	PHOSPHOR BRONZE	1	Ag-Plating	<1.5: ±0.1mm >1.5~5.0: ±0.25mm >5.0: ±0.3mm	ANGULAR ±1°	1						
5	BUTTON(INSIDE)	LCP	1				NO	DATE	REVISIONS			BY	APPD
4	HOUSING	PPA	1		TITLE: TACT SWITCH				UNIT : MM	ROHS	DWN		
3	CONTACT	SUS	2	Ag-Plating	MODEL: TS-1110U4-040F-03				SCALE: 1:1	COMPLIANT	CHK'D		
2	COVER	SUS	1		 DONGGUANG HAOYU ELECTRONICS CO., LTD 东莞市弘皓电子有限公司						APPD		
1	BUTTON(OUTER)	RUBBEL	1										
NO.	PART	NAME	MATERIAL	QTY	FINISHING				PRO.AGL:  			REV :A0	