

FRED

Ultrafast Soft Recovery Diode, 700V, 30A


Description:

These diodes are optimized to less losses and EMI/RFI in high frequency power conditioning system. The soft recovery character of the diodes offers buffer in most applications. These devices are suited for power converters and other applications where the switching losses are not significant portion of the total losses.

Features:

- Ultrafast Recovery
- 175°C operating junction temperature
- High frequency operation
- Low IR value
- High surge capacity
- Epitaxial chip construction

Product Summary	
V_R	700 V
$I_{F(AV)}$	30 A
t_{rr}	40 ns



Applications:

- Switched mode power supply
- Inverter welding
- UPS

Absolute Maximum Ratings						
Parameter	Symbol	Test Conditions	Values			Units
Repetitive peak reverse voltage	V _{RRM}		700			V
Continuous forward current	I _{F(AV)}	T _A =110°C	30			A
Single pulse forward current	I _{FSM}	T _A =25°C	290			A
Maximum repetitive forward current	I _{FRM}	Square wave, 20kHz	150			A
Operating junction	T _j		175			°C
Storage temperatures	T _{stg}		-55 to +175			°C
Electrical characteristics (Ta=25°C unless otherwise specified)						
Parameter	Symbol	Test Conditions	Min.	Typ.	Max.	Units
Breakdown voltage	V _{BR}	I _R =100μA	700			V
Blocking voltage	V _R					
Forward voltage	V _F	I _F =30 A		1.40	1.70	V
		I _F =30 A, T _j =125°C		1.35	1.60	V
Reverse leakage current	I _R	V _R = V _{RRM}			30	μA
		T _j =150°C, V _R =700V			300	μA
Reverse recovery time	trr	I _F =0.5A, I _R =1A, I _{RR} =0.25A			55	ns
		I _F =1A,V _R =30V, di/dt =200A/us		28	40	ns
Thermal characteristics						
Parameter	Symbol	Typ	MAX			Units
Junction-to-Case	R _{thJC}	-	0.70			°C/W




Figure 1. Forward Characteristic(typ.)





Figure 2. Reverse Characteristic (typ.)

Package Information

TO-247-2 PACKAGE



Symbol	Dimensions(millimeters)	
	Min.	Max.
A	4.80	5.20
A1	2.21	2.61
A2	1.85	2.15
b	1.10	1.30
b2	1.90	2.15
c	0.50	0.75
D	20.70	21.30
D1	16.25	16.85
e	5.25	5.65
E	15.60	16.00
E1	13.06	13.46
E2	4.80	5.20
E3	1.80	2.50
L	19.62	20.22
L1	4.00	4.30
ΦP	3.40	3.80
ΦP1	7.00	7.30
S	5.95	6.35