




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.11.03	
/	N/A		/	/	/



KLK-213 F V-04 X B

2A=2.5mm²(OD=3.5±0.20mm)
04=4mm²(OD=4.5±0.20mm)
06=6mm²(OD=5.0±0.25mm)
10=10mm²(OD=6.4±0.25mm)

B:
S:
X:X
Y:Y
U:U
V=V

Specifications()

1.Voltage rating():1000V DC

2.Current rating():25A(2.5mm²)
35A(4mm²)
45A(6mm²)
60A(10mm²)

3.Withstanding voltage():3000V AC,1min ≤2mA

4.Insulation resistance():200MΩ at DC1000V

5.Protection level():IP67

6.Mating cycles 200 cycles Min

7.Salt spray test 5% NaCl 48H;

8.Temperature range():-40 ~+125

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN		VIEW:	MODEL TYPE: A 2 4mm
CHECKED		UNIT: mm/in	PART NO.: KLK-213FV-04XB
APPROVED		SIZE: A4	DWG NO.: