

FRED

Ultrafast Soft Recovery Diode, 650V, 75A

Description:

These diodes are optimized to less losses and EMI/RFI in high frequency power conditioning system. The soft recovery character of the diodes offers buffer in most applications. These devices are suited for power converters and other applications where the switching losses are not significant portion of the total losses.


Features:

- Ultrafast Recovery
- 175°C operating junction temperature
- High frequency operation
- Low IR value
- High surge capacity
- Epitaxial chip construction

Product Summary	
V_R	650 V
$I_{F(AV)}$	75 A
t_{rr}	45 ns

Applications:

- Switched mode power supply
- Free wheeling diode
- UPS



Absolute Maximum Ratings						
Parameter	Symbol	Test Conditions	Values			Units
Repetitive peak reverse voltage	V _{RRM}		650			V
Continuous forward current	I _{F(AV)}	T _A =110°C	75			A
Single pulse forward current	I _{FSM}	T _A =25°C	680			A
Maximum repetitive forward current	I _{FRM}	Square wave, 20kHz	150			A
Operating junction	T _j		175			°C
Storage temperatures	T _{stg}		-55 to +175			°C
Electrical characteristics (Ta=25°C unless otherwise specified)						
Parameter	Symbol	Test Conditions	Min.	Typ.	Max.	Units
Breakdown voltage	V _{BR}	I _R =100μA	650			V
Blocking voltage	V _R					
Forward voltage	V _F	I _F =75 A		2.00	2.75	V
		I _F =75 A, T _j =125°C		1.90	2.60	V
Reverse leakage current	I _R	V _R = V _{RRM}			50	μA
		T _j =150°C, V _R =650V			500	μA
Reverse recovery time	trr	I _F =0.5A, I _R =1A, I _{RR} =0.25A			80	ns
		I _F =1A,V _R =30V, di/dt =200A/us		32	45	ns
Thermal characteristics						
Parameter	Symbol	Typ	MAX			Units
Junction-to-Case	R _{thJC}	-	0.80			°C/W




Figure 1. Forward Characteristic(typ.)




Figure 2. Reverse Characteristic (typ.)

Package Information			
TO-247 PACKAGE			
	Symbol	Dimensions(millimeters)	
		Min.	Max.
	A	4.80	5.20
	A1	2.21	2.61
	A2	1.85	2.15
	b	1.10	1.30
	b1	2.55	2.85
	b2	1.90	2.15
	c	0.50	0.75
	D	20.70	21.30
	D1	16.25	16.85
	e	5.25	5.65
	E	15.60	16.00
	E1	13.06	13.46
	E2	4.80	5.20
	E3	1.80	2.50
	L	19.62	20.22
	L1	4.00	4.30
	ΦP	3.40	3.80
	ΦP1	7.00	7.30
	S	5.95	6.35