



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		产品pin脚变更, 图面升级整理图面	2024.11.20	阿树
A2	N/A		产品电气性能变更	2025.12.22	阿树


A



B



C



D

SPECIFICATIONS

Voltage rating:500V AC/DC
Rated Current:2AMP
Withstand Voltage: 500V AC/DC
Contact Resistance: 20mΩ Max
Insulation Resistance:1000MΩ Min
Operation Temperature: -40°c to +125°c
Contact Material: Phosphor Bronze
Contact Plating: Au or Sn Over Ni
Insulator Material: Polyester(UL94V-0)
Standard:
PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260° for 10 seconds)

PART NO.:

X4611 F V-06-C63 D28
① ② ③ ④ ⑤ ⑥

- ①Series Number.
②Category: F-Female
③Welding Board Angle:V-Stright 180°
④Row No -Pin No:XX-02P-40P
⑤Plastic height: C=6.35mm
⑥Pin Length:D=2.8mm

poles	Dimensions(mm)		poles	Dimensions(mm)	
	A	B		A	B
02	4.30	2.00	22	44.30	42.00
03	6.30	4.00	23	46.30	44.00
04	8.30	6.00	24	48.30	46.00
05	10.30	8.00	25	50.30	48.00
06	12.30	10.00	26	52.30	50.00
07	14.30	12.00	27	54.30	52.00
08	16.30	14.00	28	56.30	54.00
09	18.30	16.00	29	58.30	56.00
10	20.30	18.00	30	60.30	58.00
11	22.30	20.00	31	62.30	60.00
12	24.30	22.00	32	64.30	62.00
13	26.30	24.00	33	66.30	64.00
14	28.30	26.00	34	68.30	66.00
15	30.30	28.00	35	70.30	68.00
16	32.30	30.00	36	72.30	70.00
17	34.30	32.00	37	74.30	72.00
18	36.30	34.00	38	76.30	74.00
19	38.30	36.00	39	78.30	76.00
20	40.30	38.00	40	80.30	78.00
21	42.30	40.00			

X4611FV-06-C63D28	PA6T	Brass	1U"Gold	X4611W
PART NO	Material	Material(pin)	Finish	Suitable XKB Wafer

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW: 	MODEL TYPE: 2.0mm BTB Connector		
CHECKED		UNIT: mm/in	PART NO.: X4611FV-06-C63D28		
APPROVED		SIZE: A4	DWG NO.: X-X4611FV-06-C63D28		
VISION CO. LIMITED			SCALE	PAGE	REVISION
			N/A	1/1	A2

XKB INDUSTRIAL PRECISION CO.,LIMITED