

-60V P-Channel Enhancement Mode MOSFET

Description

The AP100P06D uses advanced trench technology to provide excellent $R_{DS(ON)}$, low gate charge and operation with gate voltages as low as 6V. This device is suitable for use as a Battery protection or in other Switching application.

General Features

$V_{DS} = -60V$ $I_D = -100A$



$R_{DS(ON)} < -8.5m\Omega$ @ $V_{GS} = -10V$ (Type: 6.5m Ω)

Application

Lithium battery protection

Wireless impact

Mobile phone fast charging



Package Marking and Ordering Information

Product ID	Pack	Marking	Qty(PCS)
AP100P06D	TO252-3L	AP100P06D XXX YYYY	2500

Absolute Maximum Ratings ($T_C = 25^\circ C$ unless otherwise noted)

Symbol	Parameter	Value	Unit
V_{DS}	Drain-Source Voltage	-60	V
V_{GS}	Gate-Source Voltage	± 20	V
$I_D @ T_C = 25^\circ C$	Continuous Drain Current, $-V_{GS} @ -10V^1$	-100	A
$I_D @ T_C = 100^\circ C$	Continuous Drain Current, $-V_{GS} @ -10V^1$	-65	A
I_{DM}	Pulsed Drain Current ²	-300	A
EAS	Single Pulse Avalanche Energy ³	650	mJ
I_{AS}	Avalanche Current	80	A
$P_D @ T_C = 25^\circ C$	Total Power Dissipation ⁴	142	W
T_{STG}	Storage Temperature Range	-55 to 150	$^\circ C$
T_J	Operating Junction Temperature Range	-55 to 150	$^\circ C$
$R_{\theta JA}$	Thermal Resistance Junction-Ambient ¹	0.88	$^\circ C/W$
$R_{\theta JC}$	Thermal Resistance Junction-Case ¹	60	$^\circ C/W$

-60V P-Channel Enhancement Mode MOSFET
Electrical Characteristics ($T_c=25^{\circ}\text{C}$ unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BVDSS	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=-250\mu A$	-60	-72	---	V
$\Delta BVDSS/\Delta T_J$	BV_{DSS} Temperature Coefficient	Reference to 25°C , $I_D=-1\text{mA}$	---	-0.035	---	V/ $^{\circ}\text{C}$
RDS(ON)	Static Drain-Source On-Resistance ²	$V_{GS}=-10V, I_D=-20A$	---	6.8	8.5	m Ω
		$V_{GS}=-4.5V, I_D=-15A$	---	7.8	10	
VGS(th)	Gate Threshold Voltage	$V_{GS}=V_{DS}, I_D=-250\mu A$	-1.2	-1.6	-2.5	V
$\Delta V_{GS(th)}$	$V_{GS(th)}$ Temperature Coefficient		---	4.28	---	mV/ $^{\circ}\text{C}$
IDSS	Drain-Source Leakage Current	$V_{DS}=-60V, V_{GS}=0V, T_J=25^{\circ}\text{C}$	---	---	-1	uA
		$V_{DS}=-60V, V_{GS}=0V, T_J=55^{\circ}\text{C}$	---	---	-5	
IGSS	Gate-Source Leakage Current	$V_{GS}=\pm 20V, V_{DS}=0V$	---	---	± 100	nA
gfs	Forward Transconductance	$V_{DS}=-5V, I_D=-20A$	---	18	---	S
Rg	Gate Resistance	$V_{DS}=0V, V_{GS}=0V, f=1\text{MHz}$	---	4.0	---	Ω
Qg	Total Gate Charge (-4.5V)	$V_{DS}=-48V, V_{GS}=-10V, I_D=-5$	---	141	---	nC
Qgs	Gate-Source Charge		---	17	---	
Qgd	Gate-Drain Charge		---	28.6	---	
Td(on)	Turn-On Delay Time	$V_{DD}=-48V, V_{GS}=-10V, R_G=6\Omega, I_D=-1A$	---	70	---	ns
Tr	Rise Time		---	205	---	
Td(off)	Turn-Off Delay Time		---	402	---	
Tf	Fall Time		---	402	---	
Ciss	Input Capacitance	$V_{DS}=-25V, V_{GS}=0V, f=1\text{MHz}$	---	8620	---	pF
Coss	Output Capacitance		---	486	---	
Crss	Reverse Transfer Capacitance		---	288	---	
Is	Continuous Source Current ^{1,5}	$V_G=V_D=0V, \text{Force Current}$	---	---	-10	A
ISM	Pulsed Source Current ^{2,5}		---	---	-144	A
VSD	Diode Forward Voltage ²	$V_{GS}=0V, I_S=-1A, T_J=25^{\circ}\text{C}$	---	---	-1.2	V

Note :

- 1、The data tested by surface mounted on a 1 inch 2 FR-4 board with 2OZ copper.
- 2、The data tested by pulsed , pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$
- 3、The EAS data shows Max. rating . The test condition is $V_{DD}=-48V, V_{GS}=-10V, L=0.1\text{mH}, I_{AS}=-80A$
- 4、The power dissipation is limited by 150°C junction temperature
- 5、The data is theoretically the same as I_D and I_{DM} , in real applications , should be limited by total power dissipation.

Typical Characteristics




Fig.1 Typical Output Characteristics




Fig.2 Normalized $R_{DS(on)}$ vs. T_J




Fig.3 Normalized $R_{DS(on)}$ vs. T_J




Fig.4 Normalized V_{th} vs. T_J




Fig.5 Normalized Transient Impedance





Fig.6 Maximum Safe Operation Area

Package Mechanical Data-TO252-3L



Symbol	Dimensions In Millimeters		
	min.	typ.	max.
A	2.10	2.30	2.50
A1	0.00	0.064	0.128
b	0.64	0.75	0.86
c	0.45	0.52	0.60
D	6.40	6.60	6.80
D1	5.33REF		
D2	4.83REF		
D3	5.25REF		
E	5.90	6.10	6.30
e	2.286TYP		
L	9.80	10.10	10.40
L1	2.888REF		
L2	1.40	1.50	1.70
L3	1.65REF		
L4	0.60	0.80	1.00
φ	1.10	1.20	1.3
θ	0°		10°
θ1	5°		10°
θ2	5°		10°

-60V P-Channel Enhancement Mode MOSFET**Attention**

1,Any and all APM Microelectronics products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your APM Microelectronics representative nearest you before using any APM Microelectronics products described or contained herein in such applications.

2,APM Microelectronics assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all APM Microelectronics products described or contained herein.

3, Specifications of any and all APM Microelectronics products described or contained here instipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

4, APM Microelectronics Semiconductor CO., LTD. strives to supply high quality high reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

5, In the event that any or all APM Microelectronics products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

6, No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of APM Microelectronics Semiconductor CO., LTD.

7, Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. APM Microelectronics believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.

8, Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the APM Microelectronics product that you intend to use.

-60V P-Channel Enhancement Mode MOSFET

Edition	Date	Change
Rve1.0	2020/2/31	Initial release

Copyright Attribution "APM-Microelectronics"