

Features

200Watts peak pulse power (tp = 8/20μs)
SOD523 package
Bidirectional configurations
Solid-state silicon-avalanche technology
Low clamping voltage
Low leakage current
Low capacitance (Cj=75pF typ.)
Protection one data/power line to:
IEC 61000-4-2 ±30kV contact ±30kV air
IEC 61000-4-4 (EFT) 40A (5/50ns)
IEC 61000-4-5 (Lightning) 11A (8/20μs)

ZF





SOD-523

Applications

Cell Phone Handsets and Accessories
Microprocessor based equipment
Personal Digital Assistants (PDA's)
Notebooks, Desktops, and Servers
Portable Instrumentation

Absolute Maximum Rating

Rating	Symbol	Value	Units
Peak Pulse Power (t_p =8/20μs)	P_{PP}	200	Watts
Peak Pulse Current (t_p =8/20μs) (note1)	I_{pp}	11	A
ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	V_{ESD}	30 30	kV
Lead Soldering Temperature	T_L	260(10seconds)	℃
Junction Temperature	T_J	-55 to + 125	℃
Storage Temperature	T_{stg}	-55 to + 125	℃


Electrical Characteristics

Parameter	Symbol	Conditions	Min	Typical	Max	Units
Reverse Stand-Off Voltage	V_{RWM}				5.0	V
Reverse Breakdown Voltage	V_{BR}	I_T=1mA	6.0			V
Reverse Leakage Current	I_R	V_{RWM}=5V,T=25℃			1.0	μA
Peak Pulse Current	I_{PP}	tp =8/20μs			11	A
Clamping Voltage	V_C	I_{PP}=11A,t_p=8/20μs			20	V
Junction Capacitance	C_j	V_R = 0V, f = 1MHz		75		pF

Electronics Parameter

Symbol	Parameter
I_{PP}	Maximum Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_{PP}
V_{RWM}	Working Peak Reverse Voltage
I_R	Maximum Reverse Leakage Current @ V_{RWM}
V_{BR}	Breakdown Voltage @ I_T
I_T	Test Current

Note:. 8/20μs pulse waveform.



RATING AND CHARACTERISTIC CURVES

Figure 1: Peak Pulse Power vs. Pulse Time




Figure 2: Power Derating Curve




Figure3: Pulse Waveform






Figure 4: Clamping Voltage vs.Ipp



Soldering parameters


Reflow Condition		Pb-Free assembly (see as bellow)
Pre Heat	-Temperature Min ($T_{s(min)}$)	+150℃
	-Temperature Max($T_{s(max)}$)	+200℃
	-Time (Min to Max) (ts)	60-180 secs.
Average ramp up rate (Liquid us Temp (T_L) to peak)		3℃/sec. Max
$T_{s(max)}$ to T_L - Ramp-up Rate		3℃/sec. Max
Reflow	-Temperature(T_L)(Liquid us)	+217℃
	-Temperature(t_L)	60-150 secs.
Peak Temp (T_p)		+260(+0/-5)℃
Time within 5℃ of actual Peak Temp (t_p)		30 secs. Max
Ramp-down Rate		6℃/sec. Max
Time 25℃ to Peak Temp (T_P)		8 min. Max
Do not exceed		+260℃

FIG5: Reflow condition




Package Dimensions & Suggested Pad Layout

SOD523




UNIT	A	b_p	C	D	E	H_E	V	∠
mm	0.70 0.50	0.40 0.20	0.14 0.05	1.30 1.10	0.90 0.75	1.70 1.50	0.1	5°



Dimensions	Value (in mm)
G	0.85
X	0.70
X1	2.25
Y	0.80


Tape & rell specification

Tape



Symbol	Dimension (mm)
P0	4.00±0.20
P1	2.00±0.20
P2	2.00±0.20
D0	1.55±0.20
D1	0.50±0.20
E	1.55±0.25
F	3.60±0.20
W	8.00±0.20
A0	1.30±0.20
B0	2.35±0.20
K0	0.95±0.20
T	0.20±0.20

7” Reel



D2	177.0±5.0
D3	55Min.
D4	R24.6±2.0
G	R82.0±2.0
I	13.0±2.0
W1	10.20±3.0

Quantity: 3000PCS