








LEAD FREE
—PACKING TYPE:
1: TAPE AND REEL
—CONTACT AREA PLATING
1: GOLD FLASH
2: 15" AU
3: 30u" AU



PACKAGE


1. SIZE :

REEL : $\phi 380 \times 32$ mmCARTON : $400 \times 400 \times 325$ mm (LxWxH)

2. QUANTITY :

450 PCS / REEL

8 REEL / CARTON = 3,600 PCS



mat'l. code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection	product family		
ltr				tolerances unless otherwise specified		 mm scale 1:1	USB		
B				angles	linear		title		
				0°±x°			USB 3.2 TYPE C GEN2 RECEPTACLE UP RIGHT 24PIN SMT TYPE		
				dr	YUAN-YUAN BAO	06/08/22	dwg no		
				engr	YUAN-YUAN BAO	06/08/22	sheet2 of 2 size		
				chr	L-Q LEI	06/08/22	10167129		
				appd	TIM YAO	06/08/22	type Product Customer Drawing		
sheet index		revision sheet							