
Description

The HXY3419DF uses advanced trench technology and design to provide excellent $R_{DS(ON)}$ with low gate charge .Thisdevice is well suited for high current load applications.




DFN3X3-8L

General Features

V_{DS} =-30V,I_D =-32A

$R_{DS(ON)}$ <12mΩ @ V_{GS}=-10V

$R_{DS(ON)}$ <18mΩ @ V_{GS}=-4.5V



P-Channel MOSFET

Application

High side switch for full bridge converter

DC/DC converter for LCD display

Ordering Information

Product ID	Pack	Brand	Qty(PCS)
HXY3419DF	DFN3X3-8L	HXY MOSFET	5000

Absolute Maximum Ratings@Tj=25°C(unless otherwise specified)

Symbol	Parameter	Rating	Units
VDS	Drain-Source Voltage	-30	V
VGS	Gate-Source Voltage	±20	V
I_D@T_A=25℃	Drain Current, V_{GS} @ 10V	-32	A
I_D@T_A=70℃	Drain Current, V_{GS} @ 10V	-9.8	A
IDM	Pulsed Drain Current[1]	-65	A
P_D@T_A=25℃	Total Power Dissipation	3.57	W
TSTG	Storage Temperature Range	-55 to 150	℃
T_J	Operating Junction Temperature Range	-55 to 150	℃
Rthj-c	Maximum Thermal Resistance, Junction-case	6	℃/W
Rthj-a	Maximum Thermal Resistance, Junction-ambient[3]	35	℃/W

Electrical Characteristics@Tj=25°C(unless otherwise specified)

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Units
BV_{DSS}	Drain-Source Breakdown Voltage	V_{GS}=0V, I_D=-250uA	-30	-	-	V
RDS(ON)	Static Drain-Source On-Resistance[2]	V_{GS}=-10V, I_D=-15A	-	10	12	mΩ
		V_{GS}=-4.5V, I_D=-10A	-	14	18	mΩ
VGS(th)	Gate Threshold Voltage	V_{DS}=V_{GS}, I_D=-250uA	-1	-1.95	-2.5	V
g_{fs}	Forward Transconductance	V_{DS}=-10V, I_D=-6A	-	19	-	S
IDSS	Drain-Source Leakage Current	V_{DS}=-24V, V_{GS}=0V	-	-	-30	uA
IGSS	Gate-Source Leakage	V_{GS}=±20V, V_{DS}=0V	-	-	±100	nA
Q_g	Total Gate Charge	I_D=-15A	-	12.5	24	nC
Q_{gs}	Gate-Source Charge	V_{DS}=-15V	-	5.4	-	nC
Q_{gd}	Gate-Drain ("Miller") Charge	V_{GS}=-4.5V	-	5	-	nC
td(on)	Turn-on Delay Time	V_{DS}=-15V	-	4.4	-	ns
t_r	Rise Time	I_D=-15A	-	11.2	-	ns
td(off)	Turn-off Delay Time	R_G=3.3Ω	-	34	-	ns
t_f	Fall Time	V_{GS}=-10V	-	18	-	ns
C_{iss}	Input Capacitance	V_{GS}=0V	-	1345	2000	pF
Coss	Output Capacitance	V_{DS}=-15V f=1.0MHz	-	194	-	pF
C_{rss}	Reverse Transfer Capacitance		-	158	-	pF
trr	Reverse Recovery Time	I_S=-15A, V_{GS}=0V, dI/dt=100A/μs	-	12.4	-	ns
Q_{rr}	Reverse Recovery Charge		-	5	-	nC

Notes:
1.Pulse width limited by Max. junction temperature.
2.Pulse test

Typical Characteristics




Fig 1. Typical Output Characteristics




Fig 2. Typical Output Characteristics




Fig 3. On-Resistance v.s. Gate Voltage




Fig 4. Normalized On-Resistance v.s. Junction Temperature




Fig 5. Forward Characteristic of Reverse Diode




Fig 6. Gate Threshold Voltage v.s. Junction Temperature




Fig 7. Gate Charge Characteristics




Fig 8. Typical Capacitance Characteristics




Fig 9. Maximum Safe Operating Area




Fig 10. Effective Transient Thermal Impedance




Fig 11. Switching Time Waveform





Fig 12. Gate Charge Waveform

DFN3X3-8L Package Information



Symbol	Dimensions In Millimeters		
	Min.	Nom.	Max.
A	0.70	0.75	0.80
b	0.25	0.30	0.35
c	0.10	0.15	0.25
D	3.25	3.35	3.45
D1	3.00	3.10	3.20
D2	1.48	1.58	1.68
D3	-	0.13	-
E	3.20	3.30	3.40
E1	3.00	3.15	3.20
E2	2.39	2.49	2.59
e	0.65BSC		
H	0.30	0.39	0.50
L	0.30	0.40	0.50
L1	-	0.13	-
M	*	*	0.15
θ		10°	12°

Attention

■ Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.

■ HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.

■ Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

■ HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could
give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

■ In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

■ No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.

■ Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.

■ Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.