







RoHS Compliant



CIRCUIT DIAGRAM




一、Materials and electroplating specifications:
1.terminal: Brass; After nickel plating 30u",
tin plating 80u";

2. Insulator: Polyamide; Color:Black.

二、SPECIALITY:

1. RATED:30V Max/0.5A Max
2. CONTACT RESISTANCE: 100mΩ Max;
3. DIELECTRIC STRENGTH: 500V/AC 1min No Breakdown
4. INSULATION RESISTANCE:100MΩ Min. 500V DC
5. INSERTION FORCE:3.0Kgf Max
WITHDRAWAL FORCE:0.3Kgf Min
6. temperature:-20℃ to +70℃
7. Parts must comply with RoHS standards



P.C.B LAYOUT
(for reference only)

MEASURE POINT:
QUADRANT POINT (QP)
TANGENCY POINT (TP)
INTERSECTION POINT (IP)

UNLESS OTHERWISE
SPECIFIED, TOLERANCE:

X. ±0.25
X.x ±0.20
X.xx ±0.15
ANGULAR ±3°



联晟欣连接器(深圳)有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN Andy DATE 2014.12.24
CHECKED DATE
APPROVED DATE

PART NO: LCK-PJ-001

DRAWING NO:

TITLE:
PJ 插件式 4PIN 黑色主体 1.00mm
定位柱 插口 5.00mm通孔

REV: 04 SCALE: 1:1 UNIT: mm

SHEET: 1/1