





3D VIEW



推荐选5#;7#端为检测PIN

SCHEMATIC

RIGHT PACKING P.C.B LAYOUT
TOP VIEW

(<math>\phi 3.50\text{mm}</math> 3 OR 4 POLE PLUG DETAIL DRAWING)

NOTES:

1. CONTACT CURRENT RATING:1A;
2. CONTACT RESISTANCE:50m Ω MAX;
3. INSULATION RESISTANCE:100M Ω MIN;
4. DIELECTRIC WITHSTANDING:500V AC MIN;
5. DURABILITY:5000CYCLES MIN;
6. CONNECTOR MATING FORCES:2.94~29.4N(0.3~3.0kgf);
7. CONNECTOR UNMATING FORCES:2.94~29.4N(0.3~3.0kgf);

07	CONTACT F	1 PCS	PHOSPHOR BRONZE, T=0.20	Au Plated
06	CONTACT E	1 PCS	PHOSPHOR BRONZE, T=0.20	Au Plated
05	CONTACT D	1 PCS	PHOSPHOR BRONZE, T=0.20	Au Plated
04	CONTACT C	1 PCS	PHOSPHOR BRONZE, T=0.20	Au Plated
03	CONTACT B	1 PCS	PHOSPHOR BRONZE, T=0.20	Au Plated
02	CONTACT A	1 PCS	PHOSPHOR BRONZE, T=0.20	Au Plated
01	HOUSING	1 PCS	HIGH TEMPERATURE PLASTIC	BLACK,
ITEM	PART NAME	Q'TY	MATERIAL	DESCRIPTION



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ± 0.30 X.XX ± 0.25 X.XXX ± 0.15 X.* $\pm 2^{\circ}$ X.X* $\pm 0.5^{\circ}$	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: PJ-342 无头单柱 全贴	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. MOLD NO.	HYCW02-PJ342A-400B
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	HYC-2609221136
			SHEET NO.	1 OF 1