








NOTE:

1. MATERIAL:

- 1.1 INSULATOR: HIGH TEMPERATURE PLASTIC
- 1.2 CONTACT: BRONZE
- 1.3 SHELL: BRASS

2. ELECTRICAL CHARACTERISTICS:

- 2.1 CONTACT RESISTANCE: 30mΩ MAX
- 2.2 CONTACT CURRENT RATING: 1.5A
- 2.3 DIELECTRIC WITHSTANDING VOLTAGE: 100V R.M.S.
- 2.4 INSULATION RESISTANCE 100 MΩ MIN
- 2.5 OPERATING TEMPERATURE: -40°C~85°C

3. MECHANICAL CHARACTERISTICS:

- 3.1 MATING FORCE: 3.57kgf MAX
- 3.2 UNMATING FORCE: 1.02kgf MIN
- 3.3 DURABILITY: MANDATORY: 1,500 CYCLES

4. PLATING

4.1 TERMINAL:

- 50u" MIN NICKEL
- 80u" MIN Tin ON SOLDER AREA
- (1~30)u" Au ON CONTACT AREA

4.2 SHELL: 50u" MIN. NICKEL

PIN NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	D+
4	GND
5	StdA_SSRX-
6	StdA_SSRX+
7	GND_DRAIN
8	StdA_SSTX-
9	StdA_SSTX+
Shell	Shield

MANUFACTURE DWG

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS:

X.: ±0.50

X.X: ±0.30

X.XX: ±0.20

ANGLES:

X.' ±3°

X.X' ±2°

X.XX' ±1°

东莞市讯普电子科技有限公司
DongGuan XunPu Electronics Co., Ltd

TITLE: USB 3.0 AF 板上90度插板鱼叉脚(2.3规格)有卷边

PAR	USB-363C-ARDY
DWN	Lucas
CHKD	Ethan
APVD	Jacob
SCALE: 1:1	UNIT: MM
SIZE: A4	SHEET: 1F1
CUSTOMER COPY	REV: A