





NOTES:

1:MATERIAL:

1-1:STAINLESS STEEL THICKNE=0.10mm

2:FINISH:

2-1:3u"min Au PLATING ON CONTACT AREA,
1u"min Au PLATING ON SOLDER AREA,
50u"min NICKEL PLATING ON BASE AREA.

3:PRODUCT SPECIFICATIONS:

3-1:RATED CURRENT:1.0A/MAX
3-2:VOLTAGE RATING:1.50V/AC/DC/MAX
3-3:CONTACT RESISTANCE:80mΩ/MAX
3-4:OPERATING TEMPERATURE:-40°C~85°C

4:SALT SPRAY:24 HOURS

5:PACKING SPECIFICATION:REEL&TARE

6:DIMENSIONS MARKED □,CPK>1.33

7:ALL DIMENSIONS MARKED ▼ MUST BE CONTROLLED BY QC;



8:COMPLIANT TO RoHS&LEAD FREE







深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X" ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: L1.85*W0.90*H2.60mm侧接弹片	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW-TXT1850926P
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO:	HYC-2609171519
			SHEET NO.	1 OF 1


ø0.60
(PICK&PLACE AREA)




OVER PICK&PLACE AREA




RECOMMENDED PCB LAYOUT
TOLERANCE±0.05(焊盘推荐图)
(FOR REFERENCE ONLY)



METAL MASK T=0.10
TOLERANCE±0.05(钢网推荐图)
(FOR REFERENCE ONLY)





PULL OUT
IN THIS DIRECTION
引出方向



TOTAL
20LAYERS

PULL OUT
IN THIS DIRECTION/引出方向



⑤		ADHESIVE TAPE	
④		CARRIER TAPE	W12.0
③		TOP COVER	W7.50
②	1	LABLE	
①	1	ROLLER DISK	φ330
ITEM	QT'Y	NAME	SIZE



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2" X.X' ±0.5' UNIT: mm [inch] SCALE:1:1 SIZE: A4	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 包装图	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	
	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	
			SHEET NO.	1 OF 1