

TECHNICAL CHARACTERISTICS

MATERIAL: INSULATOR: PA66

FLAMMABILITY RATING: UL94V0

COLOR: GREEN

CONTACT / PLATING: Phosphor bronze / Ni+Sn ENVIRONMENTAL

OPERATING TEMPERATURE: -30°C UP TO +120°C

COMPLIANCE: LEAD FREE AND ROHS

ELECTRICAL

CURRENT RATING: 20A VDE

WORKING VOLTAGE: 250VAC 6,3A

WITHSTANDING VOLTAGE: 1,5KV 250VAC

RATED POWER ACCEPTANCE: --- 1,5KV

PROTECTION CLASS: I o II --- 1,6W


CONTACT RESISTANCE: 5/10 mΩ MAX

MECHANICAL

FUSE-LINK: 5x20 mm

PROTECTION RATE: IP00

SHOCKSAFE CATEGORY: PC1



Recommended P.C.B Layout

						 DEACON ELECTRONICS CO., LTD	
APPROVALS		DATE					
DRAWN	G.M.Chen	2014/11/26					
CHECKED				TITLE: FUSE HOLDER			
APPROVALS				PART NO.	BX5020—C		
A	NEW			UNIT: mm	SCALE: 1:1	SHEET 1 OF 1	
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE
							30~45° ±0.30 ANGLE 10~30 ±0.20 5~10 ±0.15 ~5 ±0.10
							DRAWING NO. PROJ. 