


Features

- * Ultra low leakage: nA level
- * Low clamping voltage
- * RoHS Compliant
- * REACH & SVHC Compliant
- * Halogen Compliant
- * DFN1006-2L Package



Circuit Diagram




Ordering Information

Part Number	Packaging	Reel Size
PESDNC2FD12VB	10000/Tape & Reel	7 inch

Marking Diagram: AA

Portion Electronics Parameter

Symbol	Parameter
V_{RWM}	Peak Reverse Working Voltage
I_R	Reverse Leakage Current @ V_{RWM}
V_{BR}	Breakdown Voltage @ I_T
I_T	Test Current
I_{PP}	Maximum Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_{PP}




Absolute Maximum Ratings ($T_A=25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20 μs pulse)	P_{pk}	100	W
Peak Pulse Current (8/20 μs pulse)	I_{PP}	5	A
ESD per IEC 61000-4-2 (Air)	V_{ESD}	± 30	kV
ESD per IEC 61000-4-2 (Contact)		± 30	
Operating Temperature Range	T_J	-40 to +125	$^{\circ}\text{C}$
Storage Temperature Range	T_{stg}	-55 to +150	$^{\circ}\text{C}$


Electrical Characteristics ($T_A=25^{\circ}\text{C}$ unless otherwise specified)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Reverse Working Voltage	V_{RWM}				12	V
Breakdown Voltage	V_{BR}	$I_T = 1\text{mA}$	13		16	V
Reverse Leakage Current	I_R	$V_{RWM} = 12\text{V}$			100	nA
Clamping Voltage	V_C	$I_{PP} = 1\text{A}$ (8 / 20 μs pulse)			18	V
Clamping Voltage	V_C	$I_{PP} = 5\text{A}$ (8 / 20 μs pulse)			20	V
Junction Capacitance	C_J	$V_R = 0\text{V}$, $f = 1\text{MHz}$,		8	15	pF


Typical Performance Characteristics ($T_A=25^{\circ}\text{C}$ unless otherwise Specified)



8 / 20us Pulse Waveform




IEC61000-4-2 Pulse Waveform




Power Derating Curve

DFN1006-2L Package Outline Drawing



SYM	DIMENSIONS					
	MILLIMETERS			INCHES		
	MIN	NOM	MAX	MIN	NOM	MAX
A	0.40	-	0.50	0.018	0.020	0.022
A1	-	-	0.05	0.000	0.001	0.002
b	0.45	0.50	0.55	0.018	0.020	0.022
c	0.12	0.15	0.18	0.005	0.006	0.007
D	0.99	1.02	1.05	0.037	0.039	0.041
e	0.65 BSC			0.026 BSC		
E	0.59	0.62	0.65	0.022	0.024	0.026
L	0.20	0.25	0.30	0.008	0.010	0.012
h	0.07	0.12	0.17	0.003	0.005	0.007

Suggested Land Pattern



SYM	DIMENSIONS	
	MILLIMETERS	INCHES
X	0.60	0.024
Y1	0.50	0.020
Y2	0.30	0.012
Y3	0.80	0.032
Z	1.30	0.052