








TOLERANCE:±0.05,THICKNESS:1.2mm
RECOMMENDED PCB LAYOUT



PIN NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	D+
4	GND
5	StdA_SSRX-
6	StdA_SSRX+
7	GND_DRAIN
8	StdA_SSTX-
9	StdA_SSTX+
Shell	Shield

NOTE:

1.MATERIAL:

1.1 INSULATOR:LCP UL 94V-0

1.2 CONTACT:BRONZE(T=0.20mm)

1.3 SHELL:BRASS(T=0.30mm)

2.ELECTRICAL CHARACTERISTICS:

2.1 CONTACT RESISTANCE:30mΩ MAXIMUM

2.2 CONTACT CURRENT RATING:1.5A

2.3 DIELECTRIC WITHSTANDING VOLTAGE:
500V R.M.S.

2.4 INSULATION RESISTANCE:1000 MEGOHMS MIN

2.5 OPERATING TEMPERATURE:-40°C ~ 85°C

3.MECHANICAL CHARACTERISTICS:

3.1 MATING FORCE:3.57kg MAX

3.2 UNMATED FORCE:1.02kg MIN

3.3 DURABILITY:MANDATORY:1500 CYCLES

4.PLATING

4.1 TERMINAL:

50u" MIN NICKEL ALL OVER

100u"MIN Tin ON SOLDER AREA

(1~30)u"Au ON CONTACT AREA

4.2 SHELL:50u"MIN.NICEL ALL OVER

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		 TITLE:沉板90度双排插—沉板3.3	
DECIMALS:	ANGLES:	PAR	USB-329-ARFW
X.:±0.30	±1°	DWN	Lucas
X.X:±0.20		CHKD	Ethan
X.XX:±0.15		APVD	Jacob
CUSTOMER COPY		SCALE 1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A