


Circuit Diagram

NOTE:

1.ELECTRICAL CHARACTERISTICS:

1.1 RATINGS:DC30V 1.0A

1.2 CONTACT RESISTANCE:30mΩ MAX

1.3 INSULATION RESISTANCE:100MΩ MIN

1.4 WITHSTAND VOLTAGE:AC 500V /1 Minute






1.5 WORKING TEMPERATURE:-25~+85°C

1.6 SOLDER HEAT RESISTANCE:260±5°C

2.MECHANICAL CHARACTERISTICS:

2.1 OPERATING FORCE:3~30N

2.2 SERVICE LIFE:5,000 Cycle.

P.C.B.Land Pattern
Vertical view

(∅3.50mm 4 POLE PLUG DETAIL DRAWING)

6	MEMBRANE	1	PI	YELLOW
5	TERMINAL#D	1	BRASS	PLATING AG 5U"MIN
4	TERMINAL#C	1	PHOSPHOR(CU)	PLATING AG 5U"MIN
3	TERMINAL#B	1	PHOSPHOR(CU)	PLATING AG 5U"MIN
2	TERMINAL#A	1	PHOSPHOR(CU)	PLATING AG 5U"MIN
1	HOUSING	1	PA9T	BLACK
NO.	DESCRIPTION	QTY	MATERIAL	PLATING



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X." ±2" X.X" ±0.5"	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: PJ-322C	
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO.	HYCW-PJ322C-600B
	APPROVED BY: 邱敏	DATE : 2014-02-23	MOLD NO.	
			DRAW NO:	HYC-2609210946
SCALE:1:1	SIZE: A4		SHEET NO.	1 OF 1