



REV.	DESCRIPTION	ECN NO.	NAME	DATE












RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm







SPECIFICATIONS:

1.ELECTRICAL CHARACTERISTICS:

1−1. CONTACT RESISTANCE: 30m MAX.

1−2. DIELECTRIC WITHSTANDING VOLTAGE: 100V AC FOR ONE MINUTE.

1−3. INSULATION RESISTANCE: 100M MIN. MEASURED BY 500 VDC

2.MECHANICAL CHARACTERISTICS:

2−1. INSERTION FORCE :0.5−2.0Kgf(REF.)

2−2. WITHDRAWAL FORCE :0.8−2.0Kgf(REF.)


3.LIFE TEST: 10,000 CYCLES.


4.TO CONFORM TO THE KRCONN HAZARDOUS SUBSTANCE FREE SPEC.

Part No.:	Color
UC09−0W16F00P11	白色
UC09−0G16F00P11	绿色
UC09−0D16F00P11	蓝色
UC09−0O16F00P11	橙色

PIN	SIGNAL NAME	PIN	SIGNAL NAME
A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	DP1	B7	DN2
A7	DN1	B6	DP2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND

NO.	DESCRIPTION	MATERIAL	REMARKS	QTY
6	SHELL	STAINLESS STEEL	NI Plated	1PCS
5	SHIELDING PLATE	STAINLESS STEEL	— — —	1PCS
4	MD	HIGH TEMPERATURE PLASTIC	BLACK	1PCS
3	CONTACT	COPPER ALLOY	Au/NI Plated	1SET
2	CONTACT	COPPER ALLOY	Au/NI Plated	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS





GENERAL TOLERANCE

DIM.	TOL.
X.:	±0.50
X.X:	±0.20
X.XX:	±0.10
GENERAL ANGLE:	
X.°:	±2°
X.X°:	±1°
X.XX°:	

DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD

BXCONN®

TITLE: TYPE−C 16PIN 母座 L=7.35 橙色 蓝色 绿色 白色

DWG. NO.: UC09−0X16F00P11 CHECKED: MAX

PART NO.: UC09−0X16F00P11 DRAWN: ELLA

UNIT:	SCALE:	SHEET:	DWG. SIZE:	LAYER:	APPROVED:
mm	none	1 OF 1	A4	bxconn	WILL