

MDD3134KT

20V N-Channel Enhancement Mode MOSFET

1. Description

This 20V N-channel MOSFET is based on MDD's unique device design to achieve low $R_{DS(on)}$ and fast switching and good ESD rating performance.

2. Features

- High-side switching
- Fast switching speed
- Low threshold
- Fast switching speed
- Easy to parallel
- Interfacing, Switching

3. Application



- Power switching
- Logic level shift

4. Absolute Maximum Ratings($T_A=25^{\circ}\text{C}$ unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	20	V
Gate-Source Voltage	V_{GS}	± 12	V
Continuous Drain Current	I_D	0.75	A
Pulsed Drain Current (note1)	I_{DM}	3	A
Power Dissipation (note2)	P_D	150	mW
Junction Temperature	T_J	150	$^{\circ}\text{C}$
Storage Temperature	T_{stg}	-50~+150	$^{\circ}\text{C}$
Thermal Resistance From Junction to Ambient	$R_{\theta JA}$	625	$^{\circ}\text{C/W}$

- Stresses exceeding Maximum Ratings may damage the device.
- Maximum Ratings are stress ratings only.
- Functional operation above the Recommended Operating Conditions is not implied.
- Extended exposure to stresses above the recommended Operating Conditions may affect device reliability

5. Pinning information

Pin	Symbol	Description	Simplified outline	Equivalent Circuit	Marking	Package
1	G	Gate			34K	SOT-523
2	S	Source				
3	D	Drain				

6. $T_A=25^{\circ}\text{C}$ unless otherwise specified

Symbol	Parameter	Condition	Min	Typ	Max	Unit
$V_{(BR)DSS}$	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu A$	20	—	—	V
$V_{GS(TH)}$	Gate Threshold Voltage(note3)	$V_{DS}=V_{GS}, I_D=250\mu A$	0.35	0.54	1.1	V
I_{GSS}	Gate-body Leakage	$V_{DS}=0V, V_{GS}=\pm 10V$	—	—	± 20	μA
I_{DSS}	Zero Gate Voltage Drain current	$V_{DS}=20V, V_{GS}=0V$	—	—	1	μA
$R_{DS(ON)}$	Drain-Source On-Resistance(note3)	$V_{GS}=4.5V, I_D=0.65A$	—	—	380	m Ω
		$V_{GS}=2.5V, I_C=0.55A$	—	—	450	m Ω
		$V_{GS}=1.8V, I_C=0.45A$	—	—	800	m Ω
g_{fs}	Forward trans conductance	$V_{DS}=10V, I_D=0.8A$	1	—	—	S

7. Dynamic Electrical Characteristics(note4)

Symbol	Parameter	Condition	Min	Typ	Max	Unit
C_{iss}	Input Capacitance	$V_{GS}=0V$ $V_{DS}=16V$ $f=1.0MHz$	—	—	120	pF
C_{oss}	Output Capacitance		—	—	20	pF
C_{rss}	Reverse Transfer Capacitance		—	—	15	pF

8. Switching Characteristics(note4)

Symbol	Parameter	Condition	Min	Typ	Max	Unit
$t_{d(on)}$	Turn on Delay Time	$V_{GS}=4.5V$ $V_{DD}=10V$ $I_D=0.5A$ $R_{GEN}=10\Omega$	—	6.7	—	nS
t_r	Turn on Rise Time		—	4.8	—	nS
$t_{d(off)}$	Turn Off Delay Time		—	17.3	—	nS
t_f	Turn Off Fall Time		—	7.4	—	nS

9. Source Drain Diode Characteristics

Symbol	Parameter	Condition	Min	Typ	Max	Unit
V_{SD}	Diode forward voltage(note3)	$V_{GS}=0V, I_S=0.15A$	—	—	1.2	V

Notes: 1.Repetitive Rating: Pulse width limited by maximum junction temperature

2.This test is performed with on heat sink at $T_A=25^{\circ}\text{C}$

3.Pulse Test: Pulse Width $\leq 300\mu s$, Duty Cycle $\leq 0.5\%$

4.These parameters have no way to verify

9. Electrical Characteristics Diagrams




Figure 1. Output Characteristics




Figure 2. Transfer Characteristics




Figure 3. On-resistance vs. Drain Current




Figure 4. On-resistance vs. V_GS




Figure 5. Body Diode Characteristics





Figure 6. Threshold Voltage


20V N-Channel Enhancement Mode MOSFET

10. Recommended Soldering Profile for Rectifier Diodes (PbFree)

a)Wave Soldering Profile



b)Reflow Soldering Profile(PbFreeApplication),refer to IPC/JEDEC J-STD-020





Preheat/Soak Temperature Min (T _{min}) Temperature Max (T _{max}) Time (ts) from (T _{min} to T _{max})	50 °C 200 °C 60-120 seconds
Melting Point of Solder (Sn Ag Cu)	217°C
Ramp-up Rate to 217°C (Melting Point of Solder)	3°C/sec
Time at Temp. > 217°C (Melting Point of Solder)	60–150 Sec
Peak Temperature	255±5°C
Time within 5°C below Peak Temp.	20–40 Sec
Cooling Rate	6°C/sec (max)
Time from 25°C to Peak Temp.	8min (max)

c)Manual Soldering

When using an electric soldering iron for manual soldering, it is recommended that the temperature does not exceed 300°C and the soldering time is less than 10 seconds.

11. Package Mechanical Data



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	0.700	0.900	0.028	0.035
A1	0.000	0.100	0.000	0.004
A2	0.700	0.800	0.028	0.031
b1	0.150	0.250	0.006	0.010
b2	0.250	0.350	0.010	0.014
c	0.100	0.200	0.004	0.008
D	1.500	1.700	0.059	0.067
E	0.700	0.900	0.028	0.035
E1	1.450	1.750	0.057	0.069
e	0.500 TYP.		0.020 TYP.	
e1	0.900	1.100	0.035	0.043
L	0.400 REF.		0.016 REF.	
L1	0.260	0.460	0.010	0.018
theta	0°	8°	0°	8°

12. Important Notice and Disclaimer

Microdiode Electronics (Shenzhen) reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

Microdiode Electronics (Shenzhen) makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Microdiode Electronics (Shenzhen) assume any liability for application assistance or customer product design. Microdiode Electronics (Shenzhen) does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of Microdiode Electronics (Shenzhen).

Microdiode Electronics (Shenzhen) products are not authorized for use as critical components in life support devices or systems without express written approval of Microdiode Electronics (Shenzhen).