

Transfer or duplication of this document as well as the utilization or communication of its contents are prohibited unless explicit authorization is granted. Violations will be liable for compensation. All rights reserved for patent, utility model or design registrations. 除专利予以明确授权, 否则禁止以任何形式, 复制、引用、分发本文件的程序, 侵犯专利权和设计专利的, 侵权者将承担法律责任。

FOR-1755 Rev.1.6

2

3

4






5

6

未注公差/General tolerances (mm)

0	>3	>6	>10	>18	>30	>50	>80	>120	>180	>250	>315	>400	>500	0.1/10
3	6	10	18	30	50	80	120	180	250	315	400	500		±2°
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50	

PCB LAYOUT



2	Pin	Copper	Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

UL 标准/UL Standard:	B	C	D
额定电压/电流/Rated Voltage(V)/Current(A)	300V/15	/	300/10
IEC 标准/IEC Standard:			
过压类别/Overvoltage Category/污染等级/Pollution Degree	III/3	III/2	II/2
额定电压/电流/Rated Voltage(V)/Current(A)	/	320/20	/
额定脉冲电压(KV)/Rate Impulse Voltage(KV)	/	4	/
间距/Pitch(mm)/线数范围/Poles	5.08/N=02~24P		
使用温度范围/Operating temperature(°C)	-40~+105		
符合RoHS环保要求/Conform to RoHS	Yes		

APPD: 兰春华	2022.07.19
CHKD: 龚耀志	2022.07.18
DRFT: 周锡锦	2022.07.18
A4 (inch)	

MATERIAL:		SURFACE/COLOR:	
MAT NO./REV: - / 00		MAT STATUS: 批量	
NAME			
2EDGVC-5.08-XXP-1Y-100Z(H)			
DRAWING NO.	TYPE	DRAWING STATUS	SCALE
200095831	CUSTOMER DRAWING	已发布	2:1
		SHEET	1/1

00			周锡锦	2022.07.18
REV	ECN	DESCRIPTION	DRFT	DATE

1

2

3

4

5

6