




D



- 1.Current rating: 4A/Pin
- 2.Rated Voltage: 20V DC
- 3.Insulation resistance: 100MΩ min
- 4.Contact resistance: 30mΩ max
- 5.Dielectric strength: 500V AC
- 6.Durability: 10,000cycles
- 7.Operating temperature range: -40°C ~ +85°C

E

Unless otherwise	
General Tolerance:	
X	±0.40
X.x	±0.30
X.xx	±0.20
X°	±5°
X.x°	±3°

Title: Horizontal Pitch2.0 6Pin Battery Conn
SMT 12.5×4.4×H2.8mm

Molde Code: GT-BTR20006-0280A-008C

DRAWN	CHECKED	APPROVED	DATE
Xla	Chen	Chen	2023.12.28

 品贊科技
www.dg-switch.com

REV: A0	SHEET: 1/1
---------	------------